


[See all 37 Products in Family](#)

## 25.4mm Dia f/0.75 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock #33-258 **3 In Stock**

⊖ 1 ⊕ €68<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €68,00 each                   |
| Qty 11-49      | €57,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Aspheric Lens **Type:**

### Physical & Mechanical Properties

25.40 ±0.1 **Diameter (mm):**

|                      |                           |
|----------------------|---------------------------|
| 23.9                 | Clear Aperture CA (mm):   |
| 4.00                 | Edge Thickness ET (mm):   |
| 12.22                | Center Thickness CT (mm): |
| Protective as needed | Bevel:                    |
| 99.57                | Radius R (mm):            |

## Optical Properties

|                 |   |
|-----------------|---|
| 19.10 @ 632.8nm | Effective Focal Length EFL (mm):            |
| 0.67            | Numerical Aperture NA:                      |
| 12.7            | Back Focal Length BFL (mm):                 |
| PMMA            | Substrate: <input type="checkbox"/>         |
| ±1              | Focal Length Tolerance (%):                 |
| 632.8           | Aspheric Design Wavelength (nm):            |
| Uncoated        | Coating:                                    |
| 0.75            | f#:   |
| 61.4            | Abbe Number (v <sub>d</sub> ):              |
| 1.49            | Index of Refraction (n <sub>d</sub> ):      |
| 400 - 1100      | Wavelength Range (nm):                      |
| Infinite        | Conjugate Distance:                         |
| 632.8           | Focal Length Specification Wavelength (nm): |

## Material Properties

|    |  |
|----|--|
| 70 | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
|----|--|

## Environmental & Durability Factors

|       |                             |
|-------|-----------------------------|
| 80.00 | Operating Temperature (°C): |
|-------|-----------------------------|

## Regulatory Compliance

|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 242:                  |

## Product Details

- Prescription Information Available
- Reduced Spherical Aberration
- Broadband AR Coating Option

Our molded acrylic aspheres are economical solutions for a variety of photonic applications. With available prescription information, these lenses are easily integrated into both benchtop and OEM applications. They are available uncoated and with broadband antireflection coatings. Standard diameter sizes of 0.5" and 1" allow them to be easily mounted using our full line of [lens mounts](#).

## Compatible Mounts