

[See all 12 Products in Family](#)

25.0/25.4mm Optic Dia., X-Y Translating Optic Mount



5 Axes Optical Mount



Stock #62-956 17 In Stock

- 1 + €276^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€276,00 each
Qty 5-9	€262,40 each
Qty 10+	€234,80 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Adjustable - Linear (XY)

Type of Optics:

Circular

Available in Quick Start Kit: #17-513		Note:
Physical & Mechanical Properties		
22.0	Clear Aperture CA (mm):	
64.0	Outer Diameter (mm):	
20.00	Thickness (mm):	
±1.5 in X and Y	Travel (mm):	
180	Weight (g):	
Black Anodized Aluminum	Construction:	
Threading & Mounting		
25.0 - 25.4	Size of Compatible Optics (mm):	
15.0 (Max)	Thickness of Compatible Optics (mm):	
M6 x 1.0	Compatible Post:	
Regulatory Compliance		
Exempt	RoHS 2015:	
View	Certificate of Conformance:	
Contains SVHC(s)	Reach 247:	

Product Details

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

Technical Information

