

TECHSPEC[®] 25mm 1064nm, Laser Line λ /20 High Tolerance Right Angle Mirror



Stock **#37-665** [CONTACT US](#)

-

1

+

€336^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€336,00 each
Qty 6-25	€279,00 each
Qty 26-49	€268,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General


Type:
Right Angle Mirror

Physical & Mechanical Properties	
25.00	Length of Legs (mm):
+0.00/-0.10	Dimensional Tolerance (mm):
Protective as needed	Bevel:
90	Clear Aperture (%):
35.40	Length of Hypotenuse (mm):
Optical Properties	
$\lambda/20$	Surface Flatness (P-V):
Fused Silica (Corning 7980)	Substrate:
20-10	Surface Quality:
$R_{abs} >99.8\% @ 1064nm @ 45^\circ AOI$ $R_{avg} >99.5\% @ 1046 - 1074nm @ 45^\circ AOI$	Coating Specification:
Laser Mirror (1064nm)	Coating:
1064	Design Wavelength DWL (nm):
± 1	Pyramid Tolerance (arcmin):
± 15	Angle Tolerance (arcsec):
1MW/cm ² @ 1064nm	Damage Threshold, Reference:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

PRODUCT DETAILS

- >99.5% Reflectivity at the Design Wavelength
- ± 15 Arcsecond Angular Tolerance
- High Thermal Stability Substrates

TECHSPEC® Laser Line $\lambda/20$ High Tolerance Right Angle Mirrors are designed at Nd:YAG wavelengths with durable, high reflectivity dielectric coatings. Right angle mirrors are easily mounted and integrated into systems that redirect light 90°. With ± 15 arcsecond angular tolerance and ± 1 arcminute pyramid tolerance, these laser line mirrors simplify alignment when mounting. TECHSPEC® Laser Line $\lambda/20$ High Tolerance Right Angle Mirrors feature laser induced damage threshold specifications making them ideal for demanding laser applications.



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).