


[See all 8 Products in Family](#)

# 25mm Dia., 0.21mm Thick, Chemically Strengthened SCHOTT AS 87 eco Ultra-Thin Window

See More by [SCHOTT Optical Components](#)



Stock #22-238 **20+ In Stock**

€38<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €38,00 each                   |
| Qty 11-49      | €31,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Protective Window **Type:**

### Physical & Mechanical Properties

22.50 **Clear Aperture CA (mm):**

25.00 ±0.127 **Diameter (mm):**

|                      |  |
|----------------------|--|
| 0.21 ±0.02           | <b>Thickness (mm):</b>                     |
| Protective as needed | <b>Bevel:</b>                              |
| 90                   | <b>Clear Aperture (%):</b>                 |
| 0.22                 | <b>Poisson's Ratio:</b>                    |
| 73.3                 | <b>Young's Modulus (GPa):</b>              |
| 560.00               | <b>Knoop Hardness (kg/mm<sup>2</sup>):</b> |

## Optical Properties

|                           |   |
|---------------------------|---|
| Uncoated                  | <b>Coating:</b>                             |
| <a href="#">AS 87 ECO</a> | <b>Substrate:</b> <input type="checkbox"/>  |
| 1.504                     | <b>Index of Refraction (n<sub>d</sub>):</b> |
| 80-50                     | <b>Surface Quality:</b>                     |
| 59.5                      | <b>Abbe Number (v<sub>d</sub>):</b>         |
| 200 - 3200                | <b>Wavelength Range (nm):</b>               |

## Material Properties

|      |   |
|------|---|
| 2.46 | <b>Density (g/cm<sup>3</sup>):</b>                                |
| 8.7  | <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b> |

## Regulatory Compliance

|                           |                                    |
|---------------------------|------------------------------------|
| <a href="#">Compliant</a> | <b>RoHS 2015:</b>                  |
| <a href="#">View</a>      | <b>Certificate of Conformance:</b> |
| <a href="#">Compliant</a> | <b>Reach 247:</b>                  |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Enhanced Impact, Temperature, and Scratch Resistance
- High Transmission in the Visible and NIR Spectra
- Ideal as Cover Glass for Displays and Sensors
- [SCHOTT AS 87 eco Ultra-Thin Windows](#) Also Available

Chemically Strengthened SCHOTT AS 87 eco Ultra-Thin Windows feature enhanced mechanical properties, including impact, temperature, and scratch resistance. The ultra-thin substrates allow these windows to be used in low profile designs, enabling lighter, more compact optical systems. High transmission across the visible and NIR spectra coupled with excellent surface quality enables these windows to protect a range of sensors and display technologies on the market. Chemically Strengthened SCHOTT AS 87 eco Ultra-Thin Windows are ideal for use as cover glass where frequent surface contact or handling is expected, including displays, fingerprint sensors, and touch panels.