

[See all 8 Products in Family](#)

TECHSPEC® 25mm Dia. 1030nm 45°, Yb:YAG Laser Line Mirror



Yb:YAG ZERODUR Laser Line Mirrors

Stock **#26-897** [CONTACT US](#)

⊖ 1 ⊕ €228⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | €228,00 each |
| Qty 6-25 | €205,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

4.00 +/-0.2 **Thickness (mm):**

25.00 +0.00/-0.20 **Diameter (mm):**

90 Clear Aperture (%):

30 Parallelism (arcsec):

Optical Properties

ZERODUR® Substrate: □

20-10 Surface Quality:

45 Angle of Incidence (°):

Laser Mirror (1030nm) Coating:

1030 Design Wavelength DWL (nm):

99.8 Reflection at DWL (%):

1020 - 1040 Wavelength Range (nm):

λ/10 Surface Flatness (P-V):

Coating Specification:
R_{abs} > 99.80% @ 1030nm @ 45° AOI R_{avg} > 99.5%
@ 1020 - 1040nm @ 45° AOI

Dielectric Coating Type:

20 J/cm² @ 1030nm, 20ns, 20Hz Damage Threshold, By Design: □

Regulatory Compliance

View Certificate of Conformance:

Product Details

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
- >99.8% Reflectivity at Yb:YAG Harmonic Frequencies
- High Laser Damage Threshold Specifications

Yb:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Yb:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$ these mirrors are great for applications where the optics will be exposed to fluctuating temperatures. The Yb:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Yb:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with λ/10 flatness and 20-10 surface quality. These mirrors are ideal for laser applications that include laser ablation, welding, drilling, cutting, and sintering.