

[See all 8 Products in Family](#)

**TECHSPEC® 25mm Dia., 2mm Thick, Uncoated, Lithium Fluoride (LiF) Window**



Lithium Fluoride (LiF) Windows

Stock **#19-728** **4 In Stock**

⊖ 1 ⊕ €344.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€344,00 each
Qty 11-25	€309,00 each
Qty 26-49	€292,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Protective Window **Type:**  
Crystal **Type of Window:**

**Physical & Mechanical Properties**

Clear Aperture CA (mm):

22.50

25.00 +0.00/-0.10 **Diameter (mm):**

2.00 ±0.10 **Thickness (mm):**

<3 **Parallelism (arcmin):**

Protective as needed **Bevel:**

90 **Clear Aperture (%):**

Fine Ground **Edges:**

0.33 **Poisson's Ratio:**

64.97 **Young's Modulus (GPa):**

102.00 **Knoop Hardness (kg/mm<sup>2</sup>):**

## Optical Properties

Uncoated **Coating:**

Lithium Fluoride (LiF) **Substrate:**

1.392 **Index of Refraction (n<sub>d</sub>):**

60-40 **Surface Quality:**

97.29 **Abbe Number (v<sub>d</sub>):**

Random **Axis Orientation:**

150 - 6000 **Wavelength Range (nm):**

λ/2 @ 632.8nm **Surface Flatness (P-V):**

## Material Properties

2.64 **Density (g/cm<sup>3</sup>):**

37 **Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**


## Product Details

- High Transmission from 150nm - 6μm
- Excellent Vacuum UV (VUV) Transmission
- Low Index of Refraction

Lithium Fluoride (LiF) Windows provide high, flat transmission from 150nm to 6μm. Lithium fluoride has excellent transmission in the vacuum ultraviolet (VUV) wavelength range of 150 - 200nm. Lithium fluoride also has a low index of refraction, allowing these windows to be used without an anti-reflection (AR) coating. Lithium Fluoride (LiF) Windows are ideal for use as UV transmission windows in spectroscopy applications, as a diffracting element in X-ray spectrometry, or as infrared windows for thermal imaging applications.

**Note:** Lithium fluoride is sensitive to thermal shock and is attacked by atmospheric moisture at temperatures above 400°C.

## Technical Information



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

---