

25mm Dia. HC VIS-NIR Polarizer, Mounted



Stock #90-389 **NEW** 2 In Stock

- 1 + €975^{.00}

ADD TO CART

Volume Pricing

Qty 1-10	€975,00 each
Qty 11+	€925,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

23.75 **Clear Aperture CA (mm):**

25.00 **Diameter (mm):**

Nanoparticle **Construction:**

95 **Clear Aperture (%):**

Optical Properties

Double-Side AR Coat **Coating:**

>100,000:1 (700nm)
>10,000:1 (600 to 850nm)
>1,000:1 (600 to 1000nm) **Extinction Ratio:**

Sodium Silicate Glass Doped with Glass Nanoparticles **Substrate:**

40-20 **Surface Quality:**

>78% **Transmission (%):**

<λ/4 @ 633nm per 1cm **Transmitted Wavefront, P-V:**

<1 **Beam Deviation (arcmin):**

<0.5 (to indicated edge) **Polarization Axis Mark (%):**

600 - 1000 **Wavelength Range (nm):**

Continuous block
Continuous pass
Pulse peak power
Equivalent pulse power density
10 W/cm²
25 W/cm²
12 MW/cm²
1 μJ/cm² **Damage Threshold, By Design:**

±20 **Acceptance Angle (°):**

Threading & Mounting

Anodized Aluminum Mount **Mount Thickness (mm):**

5.00 **Mount:**

Environmental & Durability Factors

-20 to +120 **Operating Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Multiple Wavelength Ranges for UV, VIS and NIR
- >100,000:1 Contrast Ratios Available
- Ideal for Use in Harsh Environments

UV, VIS-NIR, and NIR High Contrast Polarizers offer both versatility and performance over a wide range of wavelengths. These polarizers contain uniformly stretched silver nano-particles in a 220 ±25μm thick soda-lime glass laminated on a thicker soda-lime substrate for increased durability. UV, VIS-NIR, and NIR High Contrast Polarizers are ideal for harsh environments, can withstand up to 120°C, are resistant to UV-radiation and chemicals, and can be safely used in humid environments.

Technical Information

