


## 25mm Dia. High Contrast IR Polarizer



Stock #36-655 **1 In Stock**

⊖ 1 ⊕ €995<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	€995,00 each
Qty 10+	€945,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Linear Polarizer **Type:**

### Physical & Mechanical Properties

22.50 **Clear Aperture CA (mm):**

25.00 **Diameter (mm):**

Thickness (mm):  
2.00 ±0.2

Dimensional Tolerance (mm):  
+0.0/-0.2

Construction:  
Nanoparticle

Clear Aperture (%):  
90

## Optical Properties

Angle of Incidence (°):  
±20

Extinction Ratio:  
>100,000:1 (900nm - 1200nm)  
>10,000:1 (750nm - 1400nm)  
>1,000:1 (650nm - 1700nm)

Substrate:   
Soda Lime Float Glass

Transmission (%):  
>80

Transmitted Wavefront, P-V:  
< λ/4

Beam Deviation (arcmin):  
<1

Polarization Axis Mark (%):  
±2

Wavelength Range (nm):  
650 - 1700

## Environmental & Durability Factors

Operating Temperature (°C):  
-20 to +120

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)


REACH 241:  
[Compliant](#)



## Product Details

- Multiple Wavelength Ranges for UV, VIS and NIR
- >100,000:1 Contrast Ratios Available
- Ideal for Use in Harsh Environments

UV, VIS-NIR, and NIR High Contrast Polarizers offer both versatility and performance over a wide range of wavelengths. These polarizers contain uniformly stretched silver nano-particles in a 220 ±25µm thick soda-lime glass laminated on a thicker soda-lime substrate for increased durability. UV, VIS-NIR, and NIR High Contrast Polarizers are ideal for harsh environments, can withstand up to 120°C, are resistant to UV-radiation and chemicals, and can be safely used in humid environments.

## Technical Information





;