

[See all 22 Products in Family](#)

25mm Dia. x 25mm FL Protected Aluminum, Concave Mirror



Stock **#43-465** [CONTACT US](#)

⊖ 1 ⊕ €54⁵⁰

ADD TO CART

Volume Pricing

Qty 1-49	€54,50 each
Qty 50-99	€46,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Spherical Mirror **Type:**

Physical & Mechanical Properties

±0.5 **Thickness Tolerance (mm):**

25.00 ±0.50 **Diameter (mm):**

Clear Aperture (%):

90

Edge Thickness ET (mm):

3.0

Optical Properties

Coating Type:

Metal

Coating:

Protected Aluminum (400-2000nm)

Wavelength Range (nm):

400 - 2000

Effective Focal Length EFL (mm):

25.00

Substrate:

N-BK7

Aperture (f/#):

f/1

Coating Specification:

$R_{avg} > 85\%$ @ 400 - 700nm
 $R_{avg} > 90\%$ @ 400 - 2000nm

Focal Length Tolerance (%):

± 2

Radius R_1 (mm):

50.00

Surface Quality:

80-50

Radius of Curvature (mm):

50.00

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Product Details

- Ideal for Focusing Light
- Aluminum and Gold Coating Options
- Available in Sizes Ranging from 9 - 50mm

Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

Technical Information

