

## 25mm Diameter 600 Grit Ground Glass Diffuser



Stock **#38-786** 11 In Stock

-

1

+

€17<sup>.25</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €17,25 each                   |
| Qty 11+        | €15,75 each                   |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                          |                |
|----------------------------------|----------------|
| Ground Glass Diffuser            | Type:          |
| Sandblasted on first surface     | Note:          |
| Physical & Mechanical Properties |                |
| 25.00 ±0.25                      | Diameter (mm): |

|        |                                |
|--------|--------------------------------|
| Ground | Edges:                         |
| 600    | Grit: <input type="checkbox"/> |
| 1.60   | Thickness (mm):                |

Optical Properties

|             |                                     |
|-------------|-------------------------------------|
| Uncoated    | Coating:                            |
| Float Glass | Substrate: <input type="checkbox"/> |
| 350 - 2000  | Wavelength Range (nm):              |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 247:                  |


## Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- Fused Silica Substrates Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



## Quote Your Size

## Compatible Mounts