

[All Products](#) / [Optics](#) / [Beamsplitters](#) / [Broadband Non-Polarizing Cube](#)

[See all 35 Products in Family](#)

TECHSPEC® 25mm



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit

1

€284⁰⁰

ADD TO CART

Volume Pricing

Qty 1-5	€284,00 each
Qty 6-25	€227,00 each
Qty 26-99	€213,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:step
- Curve:pdf
- PDF Drawing:pdf
- IGES:igs
- eDrawing:easm
- EO Spec Sheet
- [Download All](#)

General

Type: Non-Polarizing Beamsplitter

Physical & Mechanical Properties

Bevel: Protective as needed

Clear Aperture (%): >90

Construction: Cube

Dimensions (mm): 25.0 x 25.0 x 25.0 ±0.1

Optical Properties

Beam Deviation (arcmin): ≤2

Coating: VIS

Coating Specification: R_{avg} <0.5% @ 430 - 670nm

Reflection/Transmission Ratio (R/T): 50/50

Substrate: N-BK7

Surface Quality: 40-20

Wavelength Range (nm): 430 - 670

|Ts-Tp|: <6%

Absolute Transmission (%): 25 ±10

Average Transmission (%): 25 ±5

Power (fringes) @ 632.8nm: 1.25

Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: **Compliant**

Certificate of Conformance: [View](#)

Need different specifications?

Edmund Optics offers comprehensive custom manufacturing capabilities to meet your unique requirements. Whether in the prototyping phase or full production, our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Application
s. Our experienced

Product Details

- Low Polarization Dependence: $|T_s - T_p| < 6\%$
- Constructed from High Tolerance Right Angle Prisms
- BBAR Coated Faces for Maximum Efficiency
- C-Mounted Visible and NIR **Cube Beamsplitters** Also Available


TECHSPEC® Broadband Non-Polarizing Cube Beamsplitters consist of a pair of precision high tolerance **right angle prisms** cemented together with a metallic dielectric coating on the hypotenuse of one of the prisms. The low polarization dependence of the metallic dielectric hybrid coating allows the transmission and reflection of S- and P-polarization states to be within 6% of each other. These beamsplitters feature anti-reflection (AR) coatings to maximize transmission across wavelengths ranging from 400–1620nm. TECHSPEC® Broadband Non-Polarizing Cube Beamsplitters are spectrally flat across their specified wavelength ranges, reducing effects caused by changes in the angle of incidence or converging/diverging beams. These beamsplitters are ideal for applications that require splitting of light, such as interferometers and polarimeters.

Technical Information

Related Products




Broadband Polarizing Cube Beamsplitters



Laser Line Non-Polarizing Cube Beamsplitters




Metric Prism Mounts




English Prism Mounts

Frequently Purchased Together




#47-009 - 25mm VIS, 50R/50T, Non-Polarizing Cube Beamsplitter
€312,00



#49-004 - 50mm VIS, 50R/50T, Non-Polarizing Cube Beamsplitter
€685,00



#54-638 - 300mm x 300mm, Breadboard
€212,00



#56-263 - C-Mount, 25mm Cube Mount
€292,00



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Media Type

- Application Note
- Video
- FAQ
- Glossary

APPLICATION NOTE

An Introduction to Optical Coatings

CASE STUDIES

Laser Optics for Eye Surgery

CASE STUDIES

Using IR Spectroscopy for Counterfeit Drug Detection

WEBINARS

The Ultimate Guide to Beamsplitters

APPLICATION NOTE

What are Beamsplitters?

VIDEO

Introduction to Beamsplitters

[View More](#)