

[See all 11 Products in Family](#)

## 2.8mW, 670nm, S Gated Cameo Laser



Stock #72-687 **1 In Stock**

⊖ 1 ⊕ €117<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-9	€117,00 each
Qty 10+	€111,15 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Mean Time To Failures MTTF @ 25° (hours):**  
≥120,000

**Type of Laser:**  
Diode

III R Laser Class - CDRH:

## Physical & Mechanical Properties

14 x 14 Dimensions (mm):

15 Weight (g):

24 Housing Length (mm):

## Optical Properties

670.00 Wavelength (nm):

5 Beam Diameter (mm):

< 0.5 Beam Divergence (mrad):

Red Color:

25mm - ∞ Focus Range (mm):

## Electrical

2.8 Output Power (mW):

±1.5 Power Stability (%):

## Hardware & Interface Connectivity

Free Space - Fixed Lens Standard Collimating Lens Output Type:

JST 4 Pin Connector:

4.5 Input Voltage (V):

## Environmental & Durability Factors

-10 to +55 Operating Temperature (°C):

-40 to +85 Storage Temperature (°C):

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 240:

## Product Details

- TTL Modulation up to 100kHz
- Compact 24 x 14 x 14mm Housing with M12 x 1 Threaded Barrel
- 635, 650, and 670nm Wavelength Options

Compact Gated Industrial Laser Diode Modules provide a high quality, cost effective OEM solution for a range of industrial applications. Featuring a gated CW laser output, these modules can achieve switching speeds up to 100kHz through the control input or they can be operated from low power TTL and microprocessors to achieve a simple, slow speed ON/OFF switching. An electrically isolated compact 24 x 14 x 14mm housing and M12 x 1 threaded barrel facilitates efficient cooling through good thermal contact and allows for easy integration into existing OEM laser systems. Compact Gated Industrial Laser Diode Modules are ideal for a wide range of industrial OEM applications including machine vision, inspection, positioning, and alignment. When operated within the appropriate temperature range (-10 to 55°C), these lasers can achieve long lifetimes with minimum mean time between failures (MTBF) ranging from ≥30,000 to ≥120,000 hours depending on wavelength.

**Note:** Interchangeable optics only compatible with A series Gated Cameo Lasers #72-688 and #72-689. C2 series lasers, #72-684 and #72-686, feature a fixed 2mm aperture lens, and S series lasers, #72-685 and #72-687, feature a fixed standard collimating lens that produces a beam size of 5 x 1.5mm.