

[See all 3 Products in Family](#)

## 2X, Coherent® CO<sub>2</sub> Beam Expander

See More by [Coherent®](#)



CO<sub>2</sub> Beam Expanders

Stock **#11-363** [CONTACT US](#)

⊖ 1 ⊕ €1.015<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€1.015,00 each
Qty 5-9	€920,00 each
Qty 10-24	€815,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Beam Expander **Type:**  
Fixed Magnification **Style:**

#### Physical & Mechanical Properties

53.65	Length (mm):
60	Weight (g):
30.48	Housing Diameter (mm):
Optical Properties	
11.43	Entrance Aperture (mm):
22.86	Exit Aperture (mm):
2X	Expansion Power:
Zinc Selenide (ZnSe)	Substrate: <input type="checkbox"/>
>99.4	Transmission (%):
0	Angle of Incidence (°):
High-Efficiency Anti-Reflective Coating (10.6µm)	Coating:
10600	Design Wavelength DWL (nm):
10400 - 10600	Wavelength Range (nm):
R <sub>abs</sub> <0.2% @ 10.6µm	Coating Specification:
Rotating Optics	Divergence Adjustment:

## Threading & Mounting

Input: Male M25 x 1	Mounting Threads:
---------------------	-------------------

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">Compliant</a>	Reach 224:
<a href="#">View</a>	Certificate of Conformance:

## Product Details

- Designed for CO<sub>2</sub> Laser Sources at 10.6µm
- Compact Housing for Easy System Integration
- Coherent® Infrared ZnSe Optical Elements

Coherent® CO<sub>2</sub> Beam Expanders are designed to collimate and improve the energy distribution of high power CO<sub>2</sub> laser beams. Featuring premier grade Zinc Selenide (ZnSe) optical elements from Coherent®, these beam expanders provide minimum beam deviation and greater than 99.4% transmission at 10.6µm. A high-efficiency anti-reflective coating on the ZnSe substrates results in reflectance less than 0.2% per surface and absorbance less than 0.1% per surface at 10.6µm. Coherent® CO<sub>2</sub> Beam Expanders feature a compact housing design with M25 input threading for easy integration into CO<sub>2</sub> laser systems. For additional expansion power options, please [contact us](#).

**Note:** II-VI Incorporated is now Coherent Corp.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools