

[All Products](#) / [Laser Optics](#) / [Laser Optics](#) / [405nm Laser Line Coated Plano-Convex](#)

[See all 102 Products in Family](#)

TECHSPEC®

30.0mm Diameter

PCX Lens

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



Stock #26-126 **8 In Stock** [Other Coating Options](#)

1

€66^{,00}

ADD TO CART

Product Downloads

- STEP:step
- PDF Drawing:pdf
- ISO 10110 Drawing
- IGES:igs
- Zemax:zar
- Zemax:zmx
- eDrawing:eprt
- Code V:seq
- EO Spec Sheet
- [Download All](#)

633nm Laser Line Coated Plano-Convex (PCX) Lenses



Volume Pricing	
Qty 1-9	€66,00 each
Qty 10-25	€59,50 each
Qty 26-49	€52,50 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

General

Type: Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):	30.00 +0.0/-0.025	Centering (arcmin):	<1
Center Thickness CT (mm):	6.00 ±0.10	Edge Thickness ET (mm):	3.78
Clear Aperture CA (mm):	29	Bevel:	Protective as needed

Optical Properties

Effective Focal Length EFL (mm):	100.00 @ 587.6nm	Back Focal Length BFL (mm):	96.01
Coating:	Laser V-Coat (405nm)	Coating Specification:	R _{abs} <0.25% @ 405nm
Substrate: ⓘ	N-BK7	Surface Quality:	40-20
Power (P-V) @ 632.8nm:	1.5λ	Irregularity (P-V) @ 632.8nm:	λ/4
Focal Length Tolerance (%):	±1	Radius R ₁ (mm):	51.68
f/#:	3.33	Numerical Aperture NA:	0.15

Design 405
Wavelength
DWL (nm):

Damage 3 J/cm² @
Threshold, By 405nm, 10ns
Design: ⓘ

Regulatory Compliance

RoHS 2015: **Compliant**

Reach 235: **Compliant**

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- <0.25% Reflection at 405nm for Diode Applications
- BBAR Coating Options Also Available: [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- 405nm, [532nm](#), [633nm](#), [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® 405nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 405nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [532nm](#), [633nm](#), [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information

Related Products



Laser Lenses



Plano-Convex (PCX) Lenses



Laser Optics



Laser Sources

Resources

Media Type

- Application Note
- Technical Tool
- Video
- FAQ
- Trending in Optics
- Glossary
- Scientific Paper
- Published Article

APPLICATION NOTE

TECHNICAL TOOL

VIDEO

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Polarization
Directed Flat
Lenses Product
Review

FAQ

What is the
best lens for
focusing or
collimating th...

TRENDING IN OPTICS

Free-Space
Optical
Communication

APPLICATION NOTE

Common Laser
Optics
Materials

[View More](#)