

[See all 13 Products in Family](#)

**TECHSPEC® 30mm ID Standard Cage Plate with 1/4-20 for Post Mounting**



25mm Basic Cage Plate, #88-196



Stock #85-631 **1 In Stock**

⊖ 1 ⊕ €44.<sup>50</sup>

**ADD TO CART**

|                |                               |
|----------------|-------------------------------|
| Volume Pricing |                               |
| Qty 1+         | €44,50 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Fixed **Function:**

**Physical & Mechanical Properties**

30.0 **Plate Inner Diameter (mm):**

**Bolt Circle Diameter for 6mm Dia. Thru (mm):**

38.0

**Bolt Circle Diameter for M3 C'bore (mm):**

38.0

**Construction:**

Black Anodized Aluminum

**Diameter Tolerance (mm):**

+0.025/-0.000 (inner diameter)

**Dimensions (mm):**

50 Dia.

**Thickness (mm):**

10.00

## Threading & Mounting

**Compatible Post:**

1/4-20

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**REACH 241:**

[Compliant](#)

## Product Details

- Fundamental for Basic Cage System Structure
- 50mm Diameter or 2" Square
- Anodized Aluminum Construction

TECHSPEC® Cage System Mounting Plates are fundamental components of TECHSPEC® Cage Systems. Each plate has four 6mm rod holes for constructing a basic cage system structure. Rods are mounted within 38mm bolt circles for a 26.9mm separation, and are secured in place using the included M3 x2.5 set screws. TECHSPEC® Cage System Mounting Plates includes three M3 x6 set screws for securing optical components, [cage system tubes](#), or mounts within the plate's inner diameter. These plates are constructed of black anodized aluminum and have dimensions and diameters.

### Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [Interchangeable Optical Mount and Side Access Mounting Plate](#) and [Four-Rod Insertion Plate](#)