

[See all 10 Products in Family](#)

# 330mm, 515-540nm JENar™ F-Theta Scanning Lens

See More by [Jenoptik](#)



Stock #16-774 **5 In Stock**

⊖ 1 ⊕ €1.110<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€1.110,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

017700-208-26 **Model Number:**

JENar F-Theta **Type:**

**Note:**  
Damage Warning: Not recommended for picosecond and femtosecond laser pulses.

**Protective Window:**  
[#17-685](#): One Included

Manufacturer:

Jenoptik

## Physical & Mechanical Properties

119.8 +0/-0.2      **Maximum Diameter (mm):**

1300      **Weight (g):**

426.1      **Flange Distance (mm):**

16      **Input Beam Diameter, 1/e<sup>2</sup> (mm):**

62.1      **Maximum Length (mm):**

## Optical Properties

330.00      **Focal Length FL (mm):**

57.6      **Scan Angle (°):**

245 x 245      **Scan Field (mm):**

F-Theta Only: 18.4  
With Scanner: 18.4      **Telecentricity (°):**

384.1      **Working Distance (mm):**

515 - 540      **Wavelength Range (nm):**

**Damage Threshold, By Design:**   
2.5 J/cm<sup>2</sup> \* (τ/[ns])<sup>0.35</sup>  
2.5 MW/cm<sup>2</sup>

347      **Scan Field Diameter (mm):**

23      **Focus Size Diameter, 1/e<sup>2</sup> (μm):**

6810      **GDD Specification (fs<sup>2</sup>):**

2.5 J/cm<sup>2</sup> \* (τ/[ns])<sup>0.35</sup>      **Damage Threshold, Pulsed:**

2.5 MW/cm<sup>2</sup>      **Damage Threshold, CW:**

## Threading & Mounting

M85 x 1      **Mounting Threads:**

## Regulatory Compliance

[View](#)      **Certificate of Conformance:**

## Product Details

- Ideal for High-Precision Material Processing and Laser Scanning Applications
- Large Scan Fields Up to 320mm x 320mm
- Wide Range of Focal Lengths from 108mm - 330mm
- [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) Also Available

Jenoptik JENar™ F-Theta Scanning Lenses are designed to provide flat field at the image plane of scanning systems and are used in conjunction with [galvanometers](#), [beam expanders](#), and [laser sources](#). These F-Theta lenses feature a wide range of focal lengths and large scan fields. Optimized for common Nd:YAG, Yb:doped, and fiber laser sources, these lenses are available in wavelength ranges of 355nm, 515-540nm, and 1030-1080nm. With their patented stackable mounting technology, these lenses compensate for thermal stresses and improve the stability of the optical components, ensuring high-precision adjustment and position control in OEM systems. Jenoptik JENar™ F-Theta Scanning Lenses are ideal for high-precision laser material processing and laser scanning applications.

[Contact us](#) if your application requires Jenoptik JENar™ F-Theta Scanning Lenses or [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) not shown on our website.