

[See all 6 Products in Family](#)

35mm FL SWIR Series Fixed Focal Length Lens



Stock **#68-689** [CONTACT US](#)

-

1

+

 €2.286^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€2.286,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Series:

1" SWIR Series Fixed Focal Length Lenses

Type:

Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:

Variable

Length (mm):

43.00

42.0	Maximum Diameter (mm):
42	Outer Diameter (mm):
135	Weight (g):

Optical Properties

100.00	Field of View @ Min Working Distance (mm):
20.9°	Horizontal Field of View, 1" Sensor:
16.00	Maximum Image Circle (mm):
35.00	Focal Length FL (mm):
300 - ∞	Working Distance (mm):
f/1.4 - f/16	Aperture (f/#):
<-0.5	Distortion (%):
-0.5	Maximum Distortion (%):

SWIR	Lens Wavelength Range:
------	------------------------

Sensor

1"	Maximum Sensor Format:
4.50	Pixel Size (µm):

Threading & Mounting

M35.5 x 0.50	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- 1", C-Mount Lens
- Spectral Range of 800 - 2000nm for InGaAs SWIR Sensors
- 8mm to 50mm Focal Lengths

Short Wave Fixed Focal Length Lenses are the best choice for use with SWIR cameras. The SWIR spectrum is an ideal choice for a variety of applications, including solar cell inspection, security, and biomedical imaging. When utilized in conjunction with a SWIR camera, these lenses will permit imaging through silicon, imaging outdoors without additional illumination, detecting bruising on fruit, and a host of additional infrared applications.

Technical Information



