

[See all 8 Products in Family](#)

# 38.1mm Dia. x 250mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF<sub>2</sub>) PCX Lens | CF-PX-38-250

See More by [ISP Optics](#)



Stock #24-810 CLEARANCE **3 In Stock**

1  €303<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€303,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Plano-Convex Lens **Type:**

CF-PX-38-250 **Model Number:**

### Physical & Mechanical Properties

**Diameter (mm):**

38.10 +0.00/-0.13

<3 **Centering (arcmin):**

3.80 ±0.20 **Center Thickness CT (mm):**

3.80 **Edge Thickness ET (mm):**

34.29 **Clear Aperture CA (mm):**

Protective as needed **Bevel:**

### Optical Properties

250.00 @5µm **Effective Focal Length EFL (mm):**

Uncoated **Coating:**

Calcium Fluoride (CaF<sub>2</sub>) **Substrate:**

60-40 **Surface Quality:**

λ **Irregularity (P-V) @ 632.8nm:**

±2 **Focal Length Tolerance (%):**

100.00 **Radius R<sub>1</sub> (mm):**

6.56 **f#:**

0.08 **Numerical Aperture NA:**

300 - 8000 **Wavelength Range (nm):**

### Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 240:**

## Product Details

- Greater than 90% Transmission from 0.35-7µm
- Low Index of Refraction
- Ideal for Integration into Infrared Systems

ISP Optics Calcium Fluoride Plano-Convex (PCX) Lenses provide greater than 90% transmission from 350nm to 7µm and feature a low refractive index, allowing them to be used without an Anti-Reflection (AR) coating. Calcium Fluoride features a high laser damage threshold and low stress birefringence, making them highly suitable for integration into infrared systems. Additionally, calcium fluoride features low solubility and offers superior hardness to comparable fluoride-based substrates, making these PCX lenses capable of withstanding harsh environments and exposure to the elements. ISP Optics Calcium Fluoride Plano-Convex (PCX) Lenses are ideal for demanding applications that require superior performance from the visible through the mid-wave infrared (MMR) spectra.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools