


[See all 16 Products in Family](#)

TECHSPEC<sup>®</sup>

4" Dia.  $\lambda$ /20 Fused Silica Dual Surface Flat



Stock **#48-132** 20+ In Stock

-

1

+

€1.715<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €1.715,00 each                |
| Qty 6-10       | €1.545,00 each                |
| Qty 11-25      | €1.460,00 each                |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Interferometry Window

Type:

Includes a certificate of calibration.

Note:

| Physical & Mechanical Properties |                          |
|----------------------------------|--------------------------|
| 91.40                            | Clear Aperture CA (mm):  |
|                                  |                          |
| 4.00 ±0.04                       | Diameter (inches):       |
|                                  |                          |
| 101.60 ±1.0                      | Diameter (mm):           |
|                                  |                          |
| 0.75 ±0.06                       | Thickness (inches):      |
|                                  |                          |
| 19.05 ±1.5                       | Thickness (mm):          |
|                                  |                          |
| ≤1                               | Parallelism (arcmin):    |
|                                  |                          |
| Protective as needed             | Bevel:                   |
|                                  |                          |
| Dual Surface                     | Construction:            |
|                                  |                          |
| Fine Ground                      | Edges:                   |
|                                  |                          |
| 0.16                             | Poisson's Ratio:         |
|                                  |                          |
| 73                               | Young's Modulus (GPa):   |
|                                  |                          |
| 522.00                           | Knoop Hardness (kg/mm²): |
|                                  |                          |

| Optical Properties                          |                                        |
|---------------------------------------------|----------------------------------------|
| Uncoated                                    | Coating:                               |
|                                             |                                        |
| <a href="#">Fused Silica</a> (Corning 7980) | Substrate: <input type="checkbox"/>    |
|                                             |                                        |
| 1.458                                       | Index of Refraction (n <sub>d</sub> ): |
|                                             |                                        |
| 60-40                                       | Surface Quality:                       |
|                                             |                                        |
| 67.8                                        | Abbe Number (v <sub>d</sub> ):         |
|                                             |                                        |
| 200 - 2200                                  | Wavelength Range (nm):                 |
|                                             |                                        |
| λ/20                                        | Surface Flatness (P-V):                |
|                                             |                                        |

| Material Properties                                               |                                                              |
|-------------------------------------------------------------------|--------------------------------------------------------------|
| 2.20                                                              | Density (g/cm³):                                             |
|                                                                   |                                                              |
| 0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
|                                                                   |                                                              |
|                                                                   |                                                              |
|                                                                   |                                                              |

| Regulatory Compliance     |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
|                           |                             |
| <a href="#">Compliant</a> | Reach 197:                  |
|                           |                             |
| <a href="#">View</a>      | Certificate of Conformance: |
|                           |                             |

## Product Details

- λ/10 and λ/20 Surface Flatness Options
  - Each λ/20 Flat 76.2mm and Larger Includes a Certificate of Calibration
  - Extended Lifetime in Contact Measurement Applications
  - [Single Surface Optical Flats](#) Also Available
- TECHSPEC® Precision Dual Surface Optical Flats are precision ground and polished to the stated accuracies on both surfaces so that either face may be used for test applications. Both surfaces are tested and certified by our Zygo Interferometer. Each flat ships in a durable storage case for permanent protection. TECHSPEC® Precision Dual Surface Optical Flats specified for λ/20 flatness that are 76.2mm or larger also include a certificate of calibration. These dual surface flats are uncoated and offered in diameters ranging from 25.40 to 304.80mm.

## Compatible Mounts

