

TECHSPEC<sup>®</sup> 400-700nm OD 0.9, M25.5 x 0.5 Absorptive ND Filter



Stock #66-707 5 In Stock

-

1

+

€89<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | €89,00 each                   |
| Qty 10-25      | €80,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                        |                         |
|--------------------------------|-------------------------|
| Type:                          | Neutral Density Filter  |
| Stock No. of Unmounted Filter: | <a href="#">#46-215</a> |

| Physical & Mechanical Properties |       |
|----------------------------------|-------|
| Diameter (mm):                   | 28.00 |

|                       |                               |
|-----------------------|-------------------------------|
| 22.0                  | Clear Aperture CA (mm):       |
| Optical Properties    |                               |
| 0.9                   | Optical Density OD (Average): |
| ND Filter Glass       | Substrate: □                  |
| Uncoated              | Coating:                      |
| 12.50                 | Transmission (%):             |
| 400 - 700             | Wavelength Range (nm):        |
| Threading & Mounting  |                               |
| M25.5 x 0.50          | Filter Thread:                |
| 9.9                   | Mount Thickness (mm):         |
| Regulatory Compliance |                               |
| <a href="#">View</a>  | Certificate of Conformance:   |

## Product Details

- VIS and NIR ND Filters, Mounted for Imaging Lenses
- Variety of Optical Densities
- Stack Filters Together for Custom Transmission Profiles

Our [TECHSPEC® Absorptive Neutral Density Filters](#) and [TECHSPEC® NIR Non-Reflective Neutral Density Filters](#) are now available in M25.5 and M30.5 mounts for imaging lenses. Neutral Density (ND) filters are useful for limiting the amount of light that reaches the sensor of a camera. Using ND filters rather than the iris of your lens allows the imaging system to limit the depth of field of the image, eliminating parallax errors and other image artifacts that may limit the usefulness of your machine vision software.

We have specially designed our mounts to hold filters up to 6.5mm in thickness, allowing the user to stack multiple ND filters together to create custom transmission filters. Optical Densities are additive, meaning a filter stack of a 0.4 OD filter and a 1.3 OD filter will produce a 1.7 Optical Density.