

TECHSPEC[®] 400, 800nm, 50.8mm Dia., Ultrafast Dual Band Mirror



Stock #24-323 9 In Stock

-

1

+

€720^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€720,00 each
Qty 6-9	€635,00 each
Qty 10+	€570,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Laser Mirror

Typical Applications:

Beam transport of 1st and 2nd harmonic of
Ti:Sapphire lasers

Physical & Mechanical Properties

Thickness (mm):

9.53 ±0.10	
	Diameter (mm):
50.80 +0/-0.1	
	Clear Aperture (%):
>88	
	Back Surface:
Commercial Polish	
	Parallelism (arcmin):
<3	

Optical Properties	
	Substrate: □
Fused Silica (JGS1)	
	Surface Quality:
10-5	
	Angle of Incidence (°):
45	
	Coating:
IBS (385-415, 770-830nm)	
	Design Wavelength DWL (nm):
400, 800	
	Wavelength Range (nm):
385 - 415, 770 - 830	
	Surface Flatness (P-V):
λ/6	
	Coating Specification:
R _s >99.9% @385-415nm R _p >99.8% @395-415nm R _s >99.9% @770-830nm R _p >99.9% @770-820nm	
	Coating Type:
S1: Dielectric S2: Stress-compensating	
	GDD Specification:
<35fs ² @ 385 - 415nm (s-pol) <50fs ² @ 395 - 415nm (p-pol) <20fs ² @ 770 - 830nm (s-pol) <40fs ² @ 770 - 810nm (p-pol)	

Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details

- High Reflectivity & Low Group Delay Dispersion (GDD) for Ultrafast Beam Steering
- Ion-Beam Sputtered (IBS) Coatings Minimize Scatter and Absorption Losses
- Near-Zero GDD for Both the First and Second Harmonics of Ti:sapphire and Yb-doped Lasers

TECHSPEC® Dual Band Low GDD Ultrafast Mirrors maintain high reflectivity and near-zero group delay dispersion over both the first and second harmonic of Ti:sapphire and Yb-doped lasers. Utilizing Ion-Beam Sputtered Coating Technology, these mirrors minimize scatter and absorption loss commonly observed when using other traditional coating application processes. TECHSPEC® Dual Band Low GDD Ultrafast Mirrors are often used in beam steering applications as they will maintain ultrashort pulse durations that can be difficult to preserve when using more conventional laser mirrors. These mirrors are ideal for second-harmonic generation (SHG) microscopy and spectroscopy applications as well as for frequency resolved optical gating (FROG).