

[See all 20 Products in Family](#)

**TECHSPEC® 45° AOI, 35.0mm Square, Cold Mirror**



TECHSPEC High Performance Cold Mirrors

Stock **#64-449** **16 In Stock**

⊖ 1 ⊕ €78.<sup>50</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	€78,50 each
Qty 10-25	€71,00 each
Qty 26-49	€67,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Cold Mirror **Type:**

**Physical & Mechanical Properties**

3.30 ±0.2 **Thickness (mm):**

**Dimensions (mm):**

35.0 x 35.0

**Dimensional Tolerance (mm):**

+0.0/-0.2

**Length (mm):**

35.00

**Width (mm):**

35.00

## Optical Properties

**Transmission (%):**

Dichroic Filter

**Coating Type:**

Dielectric

**Coating:**

Cold Mirror, 45°

**Surface Flatness (P-V):**

4 - 6λ

**Wavelength Range (nm):**

425 - 1150

**Substrate:**

[BOROFLOAT®](#)

**Angle of Incidence (°):**

45

**Coating Specification:**

R<sub>avg</sub> ≥95% @400 - 690nm and T<sub>avg</sub> ≥90% @750 -

1200nm

AR Coating: R<sub>avg</sub> <1% @700 - 1150nm

**Surface Quality:**

80-50

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 247:**



[Compliant](#)

## Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

## Technical Information



**Quote Your Size**

## Compatible Mounts

---