

[See all 18 Products in Family](#)

488nm, $\lambda/2$ Precision Zero Order Retarder



Stock #49-209 **1 In Stock**

- 1 + €755⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-5 | €755,00 each |
| Qty 6+ | €600,00 each |
| Need More? | Request Quote |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Polymer Waveplate **Type:**

Physical & Mechanical Properties

10.16 **Clear Aperture CA (mm):**

| | |
|--------|-----------------------------|
| 25.40 | Diameter (mm): |
| ±0.508 | Thickness Tolerance (mm): |
| ±0.127 | Dimensional Tolerance (mm): |

| | |
|----------------------------|---------------|
| Birefringent Polymer Stack | Construction: |
|----------------------------|---------------|

Optical Properties

| | |
|-----|-----------------------------|
| 488 | Design Wavelength DWL (nm): |
|-----|-----------------------------|

| | |
|---------------------------------------|-------------------------------------|
| Polymer Film on N-BK7 | Substrate: <input type="checkbox"/> |
|---------------------------------------|-------------------------------------|

| | |
|-----|-----------------|
| 0.5 | Reflection (%): |
|-----|-----------------|

| | |
|-------------|-------------|
| $\lambda/2$ | Retardance: |
|-------------|-------------|

| | |
|-------|------------------|
| 40-20 | Surface Quality: |
|-------|------------------|

| | |
|----------------------------|-----------------------------|
| $\leq \lambda/5$ @ 632.8nm | Transmitted Wavefront, RMS: |
|----------------------------|-----------------------------|

| | |
|---------------|-----------------------|
| $\lambda/350$ | Retardance Tolerance: |
|---------------|-----------------------|

| | |
|------|--------------------------|
| 1.00 | Beam Deviation (arcmin): |
|------|--------------------------|

| | |
|-----------------------|---|
| 500 W/cm ² | Damage Threshold, By Design: <input type="checkbox"/> |
|-----------------------|---|

| | |
|---|-------------------|
| 0 | Retardance Order: |
|---|-------------------|

Threading & Mounting

| | |
|------|-----------------------|
| 6.35 | Mount Thickness (mm): |
|------|-----------------------|

Environmental & Durability Factors

| | |
|------------|-----------------------------|
| -20 to +50 | Operating Temperature (°C): |
|------------|-----------------------------|

Regulatory Compliance

| | |
|---------------------------|------------|
| Compliant | RoHS 2015: |
|---------------------------|------------|

| | |
|----------------------|-----------------------------|
| View | Certificate of Conformance: |
|----------------------|-----------------------------|

| | |
|---------------------------|------------|
| Compliant | REACH 241: |
|---------------------------|------------|

Product Details

- $\lambda/4$ and $\lambda/2$ Retardance
- Excellent Angular Field of View
- Birefringent Polymer Stack
- High Damage Threshold of 500 W/cm²

Precision Zero Order Waveplates (Retarders) feature carefully aligned birefringent polymer sheets laminated between two precision N-BK7 windows, and are available in standard $\lambda/4$ and $\lambda/2$ options for common visible and NIR wavelengths. These polymer waveplates (retarders) offer excellent angular field of view because they are true zero-order retarders. Also, they will experience less than 1% retardance change over a $\pm 10^\circ$ angle of incidence. Each Precision Zero Order Waveplates (Retarders) is mounted in a metal ring with the fast axis clearly marked.