

[See all 130 Products in Family](#)

TECHSPEC® 4mm Dia. 355nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock #12-625 **15 In Stock**

⊖ 1 ⊕ €118.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€118,00 each
Qty 6-25	€105,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

90	Clear Aperture (%) :
Commercial Polish	Back Surface :
4.00 +0.00/-0.10	Diameter (mm) :
3.00 ±0.20	Thickness (mm) :
Optical Properties	
10-5	Surface Quality :
99.8	Reflection at DWL (%) :
R _{abs} >99.8% @ 355nm	Coating Specification :
351 - 358	Wavelength Range (nm) :
λ/10	Surface Flatness (P-V) :
Dielectric	Coating Type :
Laser Mirror (355nm)	Coating :
355	Design Wavelength DWL (nm) :
0-45	Angle of Incidence (°) :
Fused Silica (Coming 7980)	Substrate : <input type="checkbox"/>
5 J/cm ² @ 355nm, 20ns, 20Hz	Damage Threshold, Reference : <input type="checkbox"/>

Regulatory Compliance	
View	Certificate of Conformance :

Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

Note: Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts

;