


TECHSPEC[®] 5" Dia. λ /10 Fused Silica Dual Surface Flat



Stock **#71-132** [CONTACT US](#)

-

1

+

€1.802⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€1.802,50 each
Qty 6-25	€1.442,00 each
Qty 26-49	€1.351,88 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Interferometry Window		Type:
Physical & Mechanical Properties		
114.30	Clear Aperture CA (mm):	
5.00 +0.0/-0.04	Diameter (inches):	
127.00 +0.0/-1.0	Diameter (mm):	
1.00 ±0.08	Thickness (inches):	
25.40 ±2.0	Thickness (mm):	
<3	Parallelism (arcmin):	
Protective as needed	Bevel:	
Dual Surface	Construction:	
0.16	Poisson's Ratio:	
73	Young's Modulus (GPa):	
522.00	Knoop Hardness (kg/mm²):	
Optical Properties		
Uncoated	Coating:	
Fused Silica (Corning 7980)	Substrate: ☐	
1.458	Index of Refraction (n _d):	
60-40	Surface Quality:	
67.8	Abbe Number (v _d):	
200 - 2200	Wavelength Range (nm):	
λ/10	Surface Flatness (P-V):	
Material Properties		
2.20	Density (g/cm³):	
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)		
Regulatory Compliance		
View	Certificate of Conformance:	

PRODUCT DETAILS

- λ/10 and λ/20 Surface Flatness Options
- Each λ/20 Flat 76.2mm and Larger Includes a Certificate of Calibration
- Extended Lifetime in Contact Measurement Applications
- [Single Surface Optical Flats](#) Also Available

TECHSPEC® Precision Dual Surface Optical Flats are precision ground and polished to the stated accuracies on both surfaces so that either face may be used for test applications. Both surfaces are tested and certified by our Zygo Interferometer. Each flat ships in a durable storage case for permanent protection. TECHSPEC® Precision Dual Surface Optical Flats specified for λ/20 flatness that are 76.2mm or larger also include a certificate of calibration. These dual surface flats are uncoated and offered in diameters ranging from 25.40 to 304.80mm.