

[See all 32 Products in Family](#)

**TECHSPEC® 50.8mm Dia. x 50.0mm EFL, Uncoated, Concave Laser Mirror**



TECHSPEC Uncoated Concave Mirrors

Stock **#11-347** **20+ In Stock**

⊖ 1 ⊕ €226<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€226,00 each
Qty 5-9	€199,00 each
Qty 10+	€178,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Concave Mirror **Type:**

**Physical & Mechanical Properties**

50.80 +0.00/-0.20 **Diameter (mm):**

**Back Surface:**

Fine Grind

6.72 Center Thickness CT (mm):

90 Clear Aperture (%):

10.00 ±0.20 Edge Thickness ET (mm):

## Optical Properties

Uncoated Coating:

0.15λ Surface Flatness (P-V):

50.00 Effective Focal Length EFL (mm):

Fused Silica (Corning 7980) Substrate: □

0-45 Angle of Incidence (°):

100.00 Radius R<sub>1</sub> (mm):

20-10 Surface Quality:

3λ/20 Irregularity (P-V) @ 632.8nm:

100.00 Radius of Curvature (mm):

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 253:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- High Precision Fused Silica Mirror Substrates
- Large Selection of Diameters and Focal Lengths
- Custom Coating Options Available

TECHSPEC® Uncoated Concave Laser Mirrors offer high precision 20-10 surface quality ideal for laser beam focusing applications. Featuring fused silica substrates, these concave mirrors are resistant to thermal shock and are available in focal lengths from 25mm to 500mm. TECHSPEC Uncoated Concave Laser Mirrors are ideal for applications in environments with temperature fluctuations. Custom coating options including protected metal coatings and dielectric mirror coatings are available.