

[See all 12 Products in Family](#)

50mm Travel, Low Vacuum (10⁻³ Torr) Motorized Linear Stage, Integrated Controller

See More by [Zaber™](#)



Stock **#74-698** NEW CONTACT US

-

1

+

€5.180⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€5.180,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Metric	Type:
No	Encoder:
Manual Control/ LED Indicators:	
No/Yes	
Manufacturer:	
Zaber Technologies Inc.	
Model Number:	
X-LSM050A-SV1T9	
Note:	
Requires Accessory Kit, #75-301 , for operation.	
Type of Motor:	
2-Phase Stepper	

Physical & Mechanical Properties	
Linear (X)	Type of Movement:
Needle Roller Bearing	Guide System:
173.4 x 101.2	Stage Size (mm):
50.8	Travel (mm):
20	Accuracy (µm):
<12	Backlash (µm):
21.4	Height (mm):
10	Load Capacity (kg):
100	Load Capacity (N):
<3	Repeatability (µm):
0.000029 - 24	Speed (mm/s):
35	Thrust (N):
0.40	Weight (kg):

Optical Properties	
0.047	Resolution (µm):

Electrical	
350	Current (mA):
350	Maximum Operating Current (mA):

Hardware & Interface Connectivity	
Lead Screw	Type of Drive:
24-48 VDC; Power Supply w/US Plug found in accessories kit, #75-301	Power Supply:
RS-232, USB	Computer Interface:

Material Properties	
Low vacuum (10 ⁻³ Torr)	Vacuum Compatibility:

Environmental & Durability Factors	
0 to +50	Operating Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Low Vacuum (10⁻³ Torr) and High Vacuum (10⁻⁶ Torr) Options Available
- 360° Rotational, Linear, or Vertical Travel Stages, and Goniometer Options Available
- Controlled via Mnimal Feed-Through Wires

Zaber™ Vacuum Compatible Motorized Stages are designed for integration into vacuum systems and are available in high vacuum 10⁻⁶ Torr stages or low vacuum 10⁻³ Torr configurations (upon request). The stage body components are specifically engineered to limit outgassing of contaminants in the vacuum chamber, the included stepper motors are designed for thermal management in high vacuum environments, and the stages can be connected to a computer interface with minimal feed-through wires. Zaber™ Vacuum Compatible Motorized Stages are available in linear, 360° rotational, and goniometric configurations, allowing for a complete 6 Degree-of-Freedom system to be constructed in a vacuum. These stages are ideal for applications operating in high vacuum conditions, such as semiconductor manufacturing and processing, or optical coating processes.

Note: An accessories kit, [#75-301](#), is required and sold separately.

