

TECHSPEC<sup>®</sup> 50mm VIS 0°, N-BK7 Right Angle Prism (Hypotenuse Coated)



Broadband Anti-Reflection Coated Hypotenuse Prism

Stock **#34-405** 6 In Stock

-

1

+

€289<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €289,00 each                  |
| Qty 6-25       | €231,00 each                  |
| Qty 26-49      | €217,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Right Angle Prism

Type:

Physical & Mechanical Properties

+0/-0.1

Dimensional Tolerance (mm):

Bevel:

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Protective as needed                 |                                     |
| 70.70                                | Length of Hypotenuse (mm):          |
| 50.00                                | Length of Legs (mm):                |
| Optical Properties                   |                                     |
| ±15                                  | Beam Deviation (arcsec):            |
| VIS 0° (425-675nm)                   | Coating:                            |
| N-BK7                                | Substrate: <input type="checkbox"/> |
| 40-20                                | Surface Quality:                    |
| Left-Handed                          | Image Orientation:                  |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm | Coating Specification:              |
| 90                                   | Ray Deviation (°):                  |
| 350 - 2200                           | Wavelength Range (nm):              |
| 1.25                                 | Power (fringes) @ 632.8nm:          |
| 0.25                                 | Irregularity (fringes) @ 632.8nm:   |
| Regulatory Compliance                |                                     |
| Compliant                            | RoHS 2015:                          |
| View                                 | Certificate of Conformance:         |
| Compliant                            | Reach 235:                          |

Product Details



• Single Axis Retroreflector



• Right-Handed Image

• VIS and NIR Options Available


TECHSPEC® Broadband Anti-Reflection (BBAR) Coated N-BK7 Right Angle Prisms (Hypotenuse Coated) are ideal for applications that require a single axis retroreflector. These prisms feature coating options that cover the visible and near-infrared spectrum, as well as tight angular tolerances. These TECHSPEC® Broadband Anti-Reflection (BBAR) Coated N-BK7 Right Angle Prisms (Hypotenuse Coated) are also available in custom sizes.

Technical Information







Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram

# Coating Curves

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries

- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---

;