

[See all 14 Products in Family](#)

50mm x 50mm, 1.1mm Thick, <math><100 \Omega/\text{sq}</math>, ITO Coated Glass Windows



Indium Tin Oxide (ITO) Coated Conductive Windows

Stock #74-479 **NEW** 20+ In Stock

1 €65.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | €65,00 each |
| Qty 11-25 | €52,00 each |
| Qty 26-49 | €48,75 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window **Type:**

Physical & Mechanical Properties

50 x 50 ±0.2 **Dimensions (mm):**

Thickness (mm):

1.10 ±0.25

Protective as needed

Bevel:

ITO Window

Construction:

Cut and Safety Seam

Edges:

Optical Properties

S1: ITO Coating
S2: Uncoated

Coating:

Float Glass

Substrate: □

Visible Light Transmission VLT (%):
 $T_{avg} \geq 88\%$ from 400-700nm

<100 Ω/sq

Coating Specification:

400 - 700

Wavelength Range (nm):

Material Properties

<100

Surface Resistivity (Ω/ Sq):

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Electro Magnetic Interference (EMI) Shielding, Defogging, and Display Protection Applications
- 10Ω/sq and 100Ω/sq Coating Options
- 12.5, 25, 50, and 75 mm Sizes Available
- Conductive Tape Available for Prototyping

Indium Tin Oxide (ITO) Coated Conductive Windows feature an electrically conductive coating on float glass substrates and are available in sheet resistivities of 10 Ω/sq and 100 Ω/sq. A low sheet resistivity of 10 Ω/sq is ideal for applications requiring high conductivity, while the 100 Ω/sq resistivity is commonly used for improved heat dissipation and NIR transmission. Available in both round and square sizes from 12.5 to 75 mm, the windows feature up to 88% visible light transmission in the 400-700nm range. Indium Tin Oxide (ITO) Coated Conductive Windows are ideal for a wide variety of applications including display protection, EMI shielding, outdoor surveillance, de-fogging, and de-icing applications. Additionally, conductive tape is available to simplify prototyping and integration.