

**TECHSPEC® 550nm 50mm Diameter, OD 2.0 Shortpass Filter**



TECHSPEC OD 2.0 Shortpass Filters

Stock #64-664 **8 In Stock**

⊖ 1 ⊕ €240.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€240,00 each
Qty 6-25	€216,00 each
Qty 26-49	€205,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Shortpass Filter **Type:**

**Physical & Mechanical Properties**

50.00 +0.0/-0.2 **Diameter (mm):**

**Thickness (mm):**

5.00 ±0.1	
80.00	Clear Aperture (%):
<b>Optical Properties</b>	
0	Angle of Incidence (°):
≥2.0	Optical Density OD (Average):
550.00	Cut-Off Wavelength (nm):
<a href="#">Fused Silica</a> (Coming 7980)	Substrate: <input type="checkbox"/>
Traditional Coated	Coating:
575 - 725	Rejection Wavelength (nm):
40-20	Surface Quality:
>85	Transmission (%):
400 - 530	Transmission Wavelength (nm):
λ/4	Transmitted Wavefront, P-V:
±3	Slope Factor (%):
±2	Cut-Off Tolerance (%):
400 - 725	Wavelength Range (nm):

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	RoHS 2015:
<a href="#">Compliant</a>	Reach 219:
<a href="#">View</a>	Certificate of Conformance:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Sharp Cut-Off Wavelength
- High Transmission / Rejection Efficiency
- Precision Fused Silica Substrate

Our TECHSPEC® OD 2.0 Shortpass Filters are designed to have a very sharp transition from transmission to reflection, making them extremely useful in several applications. With an average transmission of 85% and an average blocking optical density of 2.0, excellent contrast can be achieved in machine vision and gauging applications. Available in a variety of cut-off wavelengths, they are ideal for fluorescence applications, separating spectral orders, and creating custom, efficient bandpass filters when combined with [TECHSPEC® OD 2.0 Longpass Filters](#). TECHSPEC® OD 2.0 Shortpass Filters have a single layer of AR coating on the back surface that enhances the overall efficiency of each filter. These filters are designed with a precision fused silica substrate.

**Note:** Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact [kits@edmundoptics.com](mailto:kits@edmundoptics.com).

## Technical Information



## Compatible Mounts