

60mm Travel, High Vacuum (10⁻⁶ Torr) Motorized Rotary Stage, Integrated Controller

See More by [Zaber™](#)



Stock **#74-704** NEW **1 In Stock**

-

1

+

€5.860⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€5.860,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Metric	Type:
No	Encoder:
Manual Control/ LED Indicators:	
No	
Manufacturer:	
Zaber Technologies Inc.	
Model Number:	
X-RSW60A-SV2T9	
Note:	
Requires Accessory Kit, #75-301 , for operation.	
Type of Motor:	
2-Phase Stepper	
Physical & Mechanical Properties	

Rotary	Type of Movement:
131.5 x 73.2	Stage Size (mm):
360	Travel (°):
0.14	Accuracy (°):
<0.04	Backlash (°):
31.7	Height (mm):
20	Load Capacity (kg):
200	Load Capacity (N):
<0.02	Repeatability (°):
<0.349	Resolution (μrad):
0.000143 - 100	Speed (°/s):
0.72	Weight (kg):
60	Table Diameter (mm):
100	Max. Continuous Torque (N⋅cm):

Electrical

950	Current (mA):
950	Maximum Operating Current (mA):

Hardware & Interface Connectivity

Precision Worm Gear	Type of Drive:
24-48 VDC; Power Supply w/US Plug found in accessories kit, #75-301	Power Supply:

RS-232, USB	Computer Interface:
-------------	---------------------

Material Properties

High vacuum (10 ⁻⁶ Torr)	Vacuum Compatibility:
-------------------------------------	-----------------------

Environmental & Durability Factors

0 to +50	Operating Temperature (°C):
----------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Low Vacuum (10⁻³ Torr) and High Vacuum (10⁻⁶ Torr) Options Available
- 360° Rotational, Linear, or Vertical Travel Stages, and Goniometer Options Available
- Controlled via Mnimal Feed-Through Wires

Zaber™ Vacuum Compatible Motorized Stages are designed for integration into vacuum systems and are available in high vacuum 10⁻⁶ Torr stages or low vacuum 10⁻³ Torr configurations (upon request). The stage body components are specifically engineered to limit outgassing of contaminants in the vacuum chamber, the included stepper motors are designed for thermal management in high vacuum environments, and the stages can be connected to a computer interface with minimal feed-through wires. Zaber™ Vacuum Compatible Motorized Stages are available in linear, 360° rotational, and goniometric configurations, allowing for a complete 6 Degree-of-Freedom system to be constructed in a vacuum. These stages are ideal for applications operating in high vacuum conditions, such as semiconductor manufacturing and processing, or optical coating processes.

Note: An accessories kit, [#75-301](#), is required and sold separately.