

[See all 9 Products in Family](#)

**TECHSPEC® 633nm, 50mm Diameter, Thin Film Laser Line Polarizer**



TECHSPEC High Energy Laser Line Polarizers

Stock **#86-714** **1 In Stock**

⊖ 1 ⊕ €1.105<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€1.105,00 each
Qty 6-25	€945,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Linear Polarizer **Type:**

**Physical & Mechanical Properties**

45.00 **Clear Aperture CA (mm):**

50.00 **Diameter (mm):**

6.00 ±0.25 **Thickness (mm):**

+0.00/-0.25 **Dimensional Tolerance (mm):**

Thin Film Dielectric **Construction:**

90 **Clear Aperture (%):**

## Optical Properties

45 ±2 **Angle of Incidence (°):**

633 **Design Wavelength DWL (nm):**

10,000:1 **Extinction Ratio:**

**Fused Silica** (Corning 7980) **Substrate:**

40-20 **Surface Quality:**

>98 (P-Polarization) **Transmission (%):**

M4 @ 633nm **Transmitted Wavefront, P-V:**

2 J/cm<sup>2</sup> @ 532nm, 10ns, S or P Polarization **Damage Threshold, By Design:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- High Extinction Ratio of 10,000:1
- 45° Angle of Incidence
- Available for Nd:YAG Harmonics and HeNe Wavelengths

TECHSPEC® Thin Film Laser Line Polarizers are used to transmit P-polarized light while reflecting S-polarized light. These polarizers with thin film dielectric coatings combine high laser damage thresholds with high extinction ratios for optimal performance in a range of laser applications. The UV grade fused silica substrate maximizes performance, while the hard anti-reflection coating makes these durable polarizers easy to clean and simple to align.

TECHSPEC® Thin Film Laser Line Polarizers have an 45° angle of incidence. The polarizers are available for common laser wavelengths.

**LASER OPTICS** MADE BY EDMUND OPTICS®  **LEARN MORE**