

6.5X Zoom Lens, 0.7X - 4.5X Range



Stock **#83-891** 1 In Stock

-

1

+

€1.665^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€1.665,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Numerical Aperture (NA) Range:
0.029 - 0.069

General

High Magnification Zoom Lens **Type:**

Physical & Mechanical Properties

500.00 **Weight (g):**

Optical Properties

9.1 - 1.4mm	Horizontal Field of View, 1/2" Sensor:
6.5:1	Zoom Ratio:
0.7X - 4.5X	Primary Magnification PMAG:
92.00	Working Distance (mm):
0.50 @ Min FOV, 1/2" Sensor 0.10 @ Max FOV, 1/2" Sensor	Distortion (%):
1.8 - 0.13	Depth of Field (mm):
VIS	Lens Wavelength Range:
Sensor	
1/2"	Maximum Sensor Format:
Threading & Mounting	
C-Mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Robust Housing with Incremental Zoom Control
 - Coaxial In-Line Illumination Option with 1/4" Fiber Port
 - High Resolution Optical Design
- The EO Precision Zoom Lenses are ideal for inspecting small details, especially electronic components. All lenses feature a robust, anodized aluminum housing, as well as an incremental (or detented) zoom for easy integration. With a working distance of 195mm, the 0.37X–2.23X lens is ideal for applications requiring a large object standoff or field of view. The 0.7X–4.5X lens features a working distance of 92mm and is available in coaxial or standard models. In addition, all 0.7X–4.5X lens models feature an option for an inner focus to allow them to image a large depth of field without moving the whole lens or object under inspection.