

[See all 10 Products in Family](#)

## 6mm Dia. x 18mm FL, Small Diameter Plastic Aspheric Lens



Stock #36-629 **20+ In Stock**

− 1 + €34.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-10	€34,00 each
Qty 11-49	€28,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Aspheric Lens **Type:**

### Physical & Mechanical Properties

6.00 ±0.20 **Diameter (mm):**

5	Clear Aperture CA (mm):
3.50	Edge Thickness ET (mm):
4.00 ±0.20	Center Thickness CT (mm):
Protective as needed	Bevel:
<b>Optical Properties</b>	
18.00 @ 550nm	Effective Focal Length EFL (mm):
0.17	Numerical Aperture NA:
14.93	Back Focal Length BFL (mm):
Acrylic V825	Substrate: <input type="checkbox"/>
±1.5	Focal Length Tolerance (%):
550	Aspheric Design Wavelength (nm):
Uncoated	Coating:
60-40	Surface Quality:
2.94	f#:
55.3	Abbe Number (v <sub>d</sub> ):
1.491	Index of Refraction (n <sub>d</sub> ):
400 - 1500	Wavelength Range (nm):
Infinite	Conjugate Distance:
550	Focal Length Specification Wavelength (nm):

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	RoHS 2015:
<a href="#">Compliant</a>	Reach 224:
<a href="#">View</a>	Certificate of Conformance:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Small Diameter Eases OEM Integration
- High Numerical Apertures
- Ideal for Medical and Diagnostic Instrumentation

Small Diameter Plastic Aspheric Lenses are designed with OEM integration in mind. The small diameters, lightweight materials, and high numerical apertures make these lenses ideal for medical devices, diagnostic instrumentation, or wearable applications. Full prescription data is available to assist in design integration.

**Note:** For custom coating requirements, please [contact us](#).

## Compatible Mounts

