

[See all 14 Products in Family](#)

## 75mm Diameter, 1.1mm Thick, <math><100 \Omega/\text{sq}</math>, ITO Coated Glass Windows



Indium Tin Oxide (ITO) Coated Conductive Windows

Stock #74-477 NEW **20+ In Stock**

⊖ 1 ⊕ €85<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€85,00 each
Qty 11-25	€68,00 each
Qty 26-49	€63,75 each
Need More?	<a href="#">Request Quote</a>

⚠ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Protective Window **Type:**

### Physical & Mechanical Properties

75.00 ±0.2 **Diameter (mm):**

**Thickness (mm):**

1.10 ±0.25

Protective as needed

**Bevel:**

ITO Window

**Construction:**

Cut and Safety Seam

**Edges:**

## Optical Properties

S1: ITO Coating  
S2: Uncoated

**Coating:**

Float Glass

**Substrate:** □

**Visible Light Transmission VLT (%):**  
 $T_{avg} \geq 88\%$  from 400-700nm

<100  $\Omega$ /sq

**Coating Specification:**

400 - 700

**Wavelength Range (nm):**

## Material Properties

<100

**Surface Resistivity ( $\Omega$ / Sq):**

## Regulatory Compliance

[View](#)

**Certificate of Conformance:**

## Product Details

- Electro Magnetic Interference (EMI) Shielding, Defogging, and Display Protection Applications
- 10 $\Omega$ /sq and 100 $\Omega$ /sq Coating Options
- 12.5, 25, 50, and 75 mm Sizes Available
- Conductive Tape Available for Prototyping

Indium Tin Oxide (ITO) Coated Conductive Windows feature an electrically conductive coating on float glass substrates and are available in sheet resistivities of 10  $\Omega$ /sq and 100  $\Omega$ /sq. A low sheet resistivity of 10  $\Omega$ /sq is ideal for applications requiring high conductivity, while the 100  $\Omega$ /sq resistivity is commonly used for improved heat dissipation and NIR transmission. Available in both round and square sizes from 12.5 to 75 mm, the windows feature up to 88% visible light transmission in the 400-700nm range. Indium Tin Oxide (ITO) Coated Conductive Windows are ideal for a wide variety of applications including display protection, EMI shielding, outdoor surveillance, de-fogging, and de-icing applications. Additionally, conductive tape is available to simplify prototyping and integration.