

[See all 173 Products in Family](#)

TECHSPEC®

85 x 120mm Silver, 4-6λ Mirror



Stock **#71-426**

CONTACT US

-

1

+

€237^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€237,00 each
Qty 6-25	€187,00 each
Qty 26-49	€175,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Flat Mirror

Physical & Mechanical Properties

Dimensions (mm):

85.00 x 120.00 +0.00/-0.25

Clear Aperture CA (mm):

76.50 x 108.00

Seamed, 0.5mm Maximum Edge Chip	Edges:
3.00 (Nominal)	Thickness (mm):
85.00	Length (mm):
120.00	Width (mm):

Optical Properties

4 - 6λ	Surface Flatness (P-V):
Float Glass	Substrate: □
60-40	Surface Quality:
R _{avg} >98% @450 - 800nm @ 0° AOI R _{avg} >98.5% @2000 - 10,000nm @ 0° AOI	Coating Specification:
Protected Silver (450-10000nm)	Coating:
Metal	Coating Type:
450 - 10000	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


Product Details

- Wide Variety of Shapes and Sizes Available
- Enhanced Aluminum, Protected Gold, and Protected Silver Coatings for high reflectivity from 450-10000nm
- [Contact Us](#) for Custom Sizes

TECHSPEC® First Surface Mirrors feature a high reflectivity coating deposited on the front surface of the glass substrate. The mirrors are available in enhanced aluminum, protected gold, and protected silver coatings for high reflectivity from 450-10000nm. The coated surface should be oriented to reflect incident light. TECHSPEC First Surface Mirrors are offered in circular, square, and rectangular dimensions. First surface mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. These first surface mirrors easily mount into a [range of optical mounts](#) to facilitate application integration.

Note: A range of mounts specifically compatible with individual TECHSPEC® First Surface Mirrors can be found on product web pages.

Technical Information



Coating Curves