

[See all 12 Products in Family](#)

# Belt Driven Stage, Carrier Adapter Plate

See More by [Zaber™](#)



Stock #23-233 **1 In Stock**

⊖ 1 ⊕ €75<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€75,00 each
Need More?	<a href="#">Request Quote</a>

⚠ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Metric **Type:**  
Zaber Technologies Inc. **Manufacturer:**

### Physical & Mechanical Properties

64.00 **Length (mm):**  
**Thickness (mm):**

9.00

64.00

Width (mm):

## Threading & Mounting

### Mounting Threads:

(2) M6, (6) M4 S.H.C.S. Counter Bore Holes; (5) M6 x 1.0, (8) M3 x 0.5 Thru; (4) M6 x 1.0, 4.0 Deep

## Regulatory Compliance

### RoHS 2015:

[Compliant](#)

### Certificate of Conformance:

[View](#)

### Reach 247:

[Compliant](#)

## Product Details

- Designed for Use with Most 40mm T-Slot Extrusion Framing Systems and Accessories
- 500mm and 1000mm Long Travel Lengths Available
- Controlled Manually or via RS-232 Serial Interface
- Integrated 400 Counts per Revolution (CPR) Motor Mounted Encoder

Zaber™ T-Slot Extrusion Belt Driven Stages are computer-controlled stages based on a modular, expandable, T-Slot extrusion structure. The stages are compatible and easily integrated with most T-Slot extrusion framing systems. Zaber™ T-Slot Extrusion Belt Driven Stages can be controlled by the [Zaber™ Programmable Joystick Controller](#) (sold separately), a computer using an optional RS-232 or USB data cable, or manually with the knob integrated into the motor unit. The stage mounting platforms include 6xM4 x0.7 mounting holes on a 25mm grid. Each stage features rotary quadrature encoders integrated into the stepper motor, with 400 Counts per Revolution (CPR) encoder resolution. The integrated rotary encoder provides closed-loop control and slip/stall detection and recovery.

**Note:** 24-48 VDC universal power supply (required), data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately as accessories.