

[See all 24 Products in Family](#)

TECHSPEC[®]

C-Mount Extension Tube Kit



Stock **#54-668** **2 In Stock**

-

1

+

€367^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€367,00 each
Qty 5-9	€323,70 each
Qty 10-25	€298,10 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
C-Mount Kit	Type:
Contents of Kit: 5mm: #54-628 , 10mm: #54-629 , 15mm: #54-630 , 50mm: #54-632 , 100mm: #54-633	
Extension Tube (Fixed)	Function:

Physical & Mechanical Properties	
30.0	Outer Diameter (mm):
22.0	Clear Aperture CA (mm):
Threading & Mounting	
C-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

Technical Information

