

[See all 10 Products in Family](#)

## C-Mount, X-Y-Z Translating Optic Mount



5 Axes Optical Mount



Stock #87-210 [CONTACT US](#)

⊖ 1 ⊕ €484.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€484,00 each
Qty 5-9	€435,60 each
Qty 10+	€401,30 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Adjustable - Linear (XYZ)

Type:

C-Mount

Type of Optics:

## Physical & Mechanical Properties

1" x 32 TPI **Clear Aperture CA (mm):**

65.0 **Outer Diameter (mm):**

34.00 **Thickness (mm):**

±2.0 in X and Y, ±1.5 in Z **Travel (mm):**

240 **Weight (g):**

Black Anodized Aluminum **Construction:**

## Threading & Mounting

**Thickness of Compatible Optics (mm):**  
Dependent on the C-Mount Circular Optic Mount used

M6 x 1.0 **Compatible Post:**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 247:**

## Product Details

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

## Technical Information

