

Coherent® High-Sensitivity Thermopile Sensor PS19 1098413 | 1W Max Power

See More by [Coherent®](#)



Coherent® High-Sensitivity Thermopile Sensors

Stock **#12-417** [CONTACT US](#)

-

1

+

€1.905⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.905,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Model Number:

PS19 Coherent Part Number: 1098413

Meter required

Type:

±1	Linearity (%):
1	Calibration Uncertainty (%):
Air	Cooling Method:
2	Response Time (s):
Compatible Meters: #35-203, #12-393, #59-978, #88-411, #66-277, #88-412	
Maximum Incident Energy Density: 50mJ/cm ² (10ns, 1064nm)	

Physical & Mechanical Properties

19	Active Area Diameter (mm):
----	----------------------------

Optical Properties

514	Calibration Wavelength (nm):
300 - 11000	Wavelength Range (nm):
0.3 - 11	Wavelength Range (μm):

Sensor

Thermopile	Type of Sensor:
------------	-----------------

Electrical

0.5	Maximum Incident Power Density (kW/cm ²):
100μW - 1W	Power Range:
1	Maximum Power (W):
10μW	Power Resolution:

Hardware & Interface Connectivity

2	Length of Cable (m):
DB-25	Computer Interface:

Environmental & Durability Factors

Yes	Thermally Stabilized:
-----	-----------------------

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Broad Spectral Range with High Sensitivity and High Resolution
 - Large Active Area Sensors up to 19mm in Diameter
 - Flat Broadband Output with No Saturation above 1mW/cm²
- Coherent® High-Sensitivity Thermopile Sensors are designed to have a broad spectral response to accommodate an array of lasers with different wavelengths. The large active area and high resolution of these thermopile sensors allows for accurate measurements of low-power lasers. A range of models are available to meet specific needs relating to thermal stability, background radiation, and air current effect. Coherent® High-Sensitivity Thermopile Sensors are designed to accurately measure the laser power of small laser diodes, HeNe lasers, and small ion lasers. Unique to this design, these sensors will not saturate when laser power exceeds 1mW/cm².