

[See all 67 Products in Family](#)

CW Series to LUCID Triton™ C-Mount Adapter with O-Ring

See More by [LUCID Vision Labs™](#)



#23-669 CW Series to LUCID Triton™ C-Mount Adapter with O-Ring



Stock #23-669 **20+ In Stock**

⊖ 1 ⊕ €53.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€53,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Thread Adapter **Type:**

Physical & Mechanical Properties

27.50 **Inner Diameter (mm):**

8.30	Total Length (mm):
38.00	Outer Diameter (mm):
24.75	Clear Aperture CA (mm):
Black Anodized Aluminum (6061-T6)	Construction:
6.00	Extension Length (mm):

Sensor

1.85	Pixel Size (µm):
------	-------------------------

Threading & Mounting

Male to Female	Mounting Threads:
C-Mount to T-Mount	Thread Type:

Environmental & Durability Factors

IPX7 and IPX9K	Environmental Rating:
----------------	------------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Product Details

- Compact 29 x 29 x 45mm Form Factor
- Global, Rolling, or Polarized CMOS Sensors
- IP67 Protection with Optional Lens Tubes

LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) Cameras provide exceptional price performance in a compact 29 x 29mm form factor. These cameras are available with Sony's Pregius™ and Starvis™ imaging sensors with up to 24.5 megapixels of resolution, as well as Sony's polarized sensor. Each imaging sensor is actively aligned during manufacturing, ensuring sharp and crisp images even in the corners. Using the accessory IP67 lens tubes (sold separately), LUCID Vision Labs Triton GigE Power over Ethernet (PoE) Cameras can operate in harsh environments where dust or water are present up to IP67 thresholds. Triton cameras are ideal for automotive, process control, and food and beverage applications.