

TECHSPEC[®] 65mm Sq, 15kg Load Capacity, 25mm Travel, English Dovetail Stage



#16-713: Dovetail Stage, 65mm SQ, English



Stock **#16-713** 13 In Stock

-

1

+

€212⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€212,00 each
Qty 10+	€186,80 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
English	
Type:	
Included Hardware: 4X 1/4"-20, 3/8"L Socket Head Cap Screws; 1X 3mm Allen Wrench; 1X 2.5mm Allen Wrench	

Physical & Mechanical Properties

Linear (X)	Type of Movement:
Dovetail	Guide System:
Center Drive	Drive Orientation:
65 x 65	Stage Size (mm):
25	Travel (mm):
0.98	Travel (inches):
Matte Black Finish Brass	Construction:
0.5	Leadscrew Pitch (mm):
15	Load Capacity (kg):
2.56 x 2.56	Stage Size (inches):

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
------------	----------------

Threading & Mounting

Mounting Threads:
(9) 1/4-20, (4) 6-32, (8) 2-56

Regulatory Compliance	
GDPR Compliance	2023-10-25
ISO 27001 Audit	2023-11-15
PCI DSS Assessment	2023-12-01
SOX Reporting	2023-12-15
Environmental Impact	2024-01-05
Health & Safety	2024-01-20
Anti-Money Laundering	2024-02-10
Equal Opportunity	2024-02-25
Consumer Protection	2024-03-10
Product Safety	2024-03-25
Financial Reporting	2024-04-10
Supply Chain Management	2024-04-25
Human Resources	2024-05-10
Customer Satisfaction	2024-05-25
Marketing Strategy	2024-06-10
Sales Performance	2024-06-25
Inventory Management	2024-07-10
Logistics Efficiency	2024-07-25
Customer Retention	2024-08-10
Product Development	2024-08-25
Quality Assurance	2024-09-10
Customer Support	2024-09-25
Employee Training	2024-10-10
Performance Metrics	2024-10-25
Customer Feedback	2024-11-10
Market Research	2024-11-25
Competitor Analysis	2024-12-10
Strategic Planning	2024-12-25
Annual Review	2025-01-10
Future Outlook	2025-01-25

RoHS 2015: [Compliant](#)

Certificate of Conformance: [View](#)

Product Details

- Compact Overall Size for System Integration
- Brass Construction for High Stiffness and up to 15kg Load Capacity
- Compatible with All TECHSPEC® Stages

TECHSPEC® High Load Capacity Dovetail Stages are a compact, cost-effective solution for linear adjustment within an optical system. These stages feature high stiffness brass construction and a hex driven movement, allowing for a low profile and compact overall size with 5, 10, and 15kg high load capacity options. The absence of tension springs and the included external plate lock ensure resistance to vibration and increase stability. TECHSPEC High Load Capacity Dovetail Stages are ideal for imaging and laser optics systems that require low profile integrated linear adjustments in demanding environments. These stages feature bolt patterns that are compatible with all TECHSPEC and comparable metric and English stages.

Technical Information



