

[See all 7 Products in Family](#)

## E Series 25mm $\frac{2}{3}$ " Format Fixed Focal Length Lens



Stock **#27-044** **2 In Stock**

€259<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€259,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

E Series **Product Family:**

### Physical & Mechanical Properties

Variable **Iris Option:**

30.83 **Length (mm):**

Outer Diameter (mm):  
25

## Optical Properties

Horizontal Field of View, 2/3" Sensor:  
19.9°

Maximum Image Circle (mm):  
11.00

Number of Elements (Groups):  
5 (4)

Focal Length FL (mm):  
25.00

Working Distance (mm):  
250 - ∞

Aperture (f/#):  
f/4 - f/16

Coating:  
λ/4 MgF<sub>2</sub>

Maximum Distortion (%):  
0.96

Lens Wavelength Range:  
VIS

## Sensor

Maximum Sensor Format:  
2/3"

Pixel Size (μm):  
2.74

## Threading & Mounting

Filter Thread:  
M22.5x0.5

Mount:  
C-Mount

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

## Product Details

- Cost Effective Solution for Systems that Require Large Depth of Field
- Up to 2/3", C-Mount Lens
- Ideal for Logistics and Barcode Scanning Applications

Edmund Optics E Series Fixed Focal Length Lenses provide an affordable fixed focal length imaging solution without compromising performance. These lenses are designed for logistics applications that need to identify product size and shape, read barcodes, and help find product locations. These systems often don't require lenses designed with more demanding specifications like large format sensor coverage and small pixels, which can be costly. Edmund Optics E Series Fixed Focal Length Lenses are a balance of performance and cost designed with a maximum format of 2/3". To maintain affordability in prototyping and mass production, the lens housings have been simplified by removing focusing mechanics. However, the focus can still be adjusted by threading the lenses into and out of the camera, then locked with a locking ring. These lenses maintain performance control with an adjustable iris ranging from f/4 to f/16.

## Technical Information



