


[See all 18 Products in Family](#)

Flat Dome Light LFXV-50IR860

See More by [CCS](#)



Stock #19-964 **1 In Stock**

⊖ 1 ⊕ €2.035⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€2.035,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Model Number:
LFXV-50IR860

Type of Illumination:
LED Illuminator

Manufacturer:
CCS

Geometry:
Flat Dome Light

Constant

Illumination Mode:

Physical & Mechanical Properties

93 x 93 x 10

Dimensions (mm):

190

Weight (g):

50 x 50

Active Area (mm):

Optical Properties

IR

Color:

855

Wavelength (nm):

Electrical

5.7

Power Consumption (W):

Hardware & Interface Connectivity

24

Input Voltage (V):

Power Supply:

Power Supply Required and Sold Separately.

- USA: [#73-491](#)
- Europe: [#73-491](#)
- Japan: [#89-513](#)
- Korea: [#33-773](#)
- China: [#73-491](#)

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Thin, Compact, and Lightweight Housing
- Available in Multiple LED Colors
- Wide Range of Sizes Including Square and Rectangular Shapes

CCS Flat Dome Lights are ideal for achieving illumination similar to Coaxial or Dome Lights in a lighter, more compact unit. While standard dome lights are good for creating a diffuse lighting environment that minimizes specular reflection, their mechanical size and imaging aperture through a small hole on top limit their use in compact applications. These flat dome lights provide the same diffuse illumination environments as a standard dome light but in a 10mm thick, flat housing with a large imaging area, greatly increasing the options for working distance, depth of focus, and field of view. CCS Flat Dome Lights can also be used at long working distances to recreate the illumination environment of a coaxial light, which is used to reduce shadowing and has minimal glare. This flexibility makes these flat dome lights suitable for a wide range of industrial and imaging applications, particularly when imaging textured, shiny, or uneven surfaces.


Technical Information

Imaging Examples

Introducing various examples using unique characteristics of the Flat Dome Lights


Electronic Components Industry

Imaging Characters on a Textured Metal Surface



Electronic Components Industry

Imaging Characters on Button Batteries



Packaging Industry

Imaging Shrink Film of Containers

