

[See all 14 Products in Family](#)

LightPath 390036 | 6.5mm Dia., 0.56 NA, BBAR (3000-5000nm), Molded IR Aspheric Lens

See More by [Lightpath®](#)



Stock #66-561 **8 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €410⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€410,00 each
Qty 11-49	€369,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

390036 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Physical & Mechanical Properties

Diameter (mm):

6.50 ±0.015	Clear Aperture CA (mm):
5.00	
	Edge Thickness ET (mm):
1.94	
	Center Thickness CT (mm):
2.50	
	Bevel:
Protective as needed	

Optical Properties

	Effective Focal Length EFL (mm):
4.00 @2500nm	
	Numerical Aperture NA:
0.56	
	Substrate: <input type="checkbox"/>
Black Diamond™ BD-2 (Ge ₂₆ Sb ₁₂ Se ₆₀)	
	Aspheric Design Wavelength (nm):
2500	
	Coating:
BBAR (3000-5000nm)	
	Coating Specification:
R _{avg} <1.0% @ 3 - 5μm	
	Surface Quality:
80-50	
	f#:
0.89	
	Index of Refraction (n_d) @ 10μm:
2.6023	
	Index of Refraction (n_d) @ 14μm:
2.5843	
	Index of Refraction (n_d) @ 4μm:
2.6210	
	Index of Refraction (n_d) @ 5μm:
2.6173	
	Wavelength Range (nm):
3000 - 5000	
	Working Distance (mm):
3.05	
	Conjugate Distance:
Infinite	
	Focal Length Specification Wavelength (nm):
2500	

Material Properties

	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
14.00	
	Density (g/cm³):
4.68	
	Thermo-optic coefficient dn/dT:
70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 μm)	
	Transformation Temperature (°C):
285.00	

Regulatory Compliance


Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Wavelength Range of 1.8 - 12μm
- Variety of Coating Options
- Mounted and Unmounted Versions

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses feature a low-cost, molded design and offer several key benefits over Germanium substrate aspheres. With a dn/dT and CTE significantly less than that of Germanium, the lenses feature a smaller change in focal length as a function of temperature change. Featuring a higher operating temperature than Germanium (which suffers 20 – 30% transmission loss at 100°C), the lenses can be used in applications including collimators for QCL lasers and as components within thermal imaging assemblies. LightPath Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses have a wavelength range of 1.8 - 12μm. These lenses are available mounted or unmounted, in a variety of coating options.

Technical Information



Compatible Mounts
