

[See all 10 Products in Family](#)

## M58.0 x 0.75 Thread, Ring Light Filter Thread Adapter



Ring Light Filter Thread Adapter. Filter Thread varies by Stock Number. (M30.5 x 0.5 Thread Shown)

Stock #56-098 CLEARANCE **1 In Stock**

€46.<sup>00</sup>

ADD TO CART

Volume Pricing	
Qty 1+	€46,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Accessory **Type of Illumination:**

#### Physical & Mechanical Properties

Anodized Aluminum **Construction:**

#### Threading & Mounting

M58.0 x 0.75 **Filter Thread:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

## Product Details

- Compatible with LED Ring Lights
- Common Filter Thread Sizes Available
- Allows for Easy Integration of LED Ring Lights

Ring Light Filter Thread Adapters allow our LED ring lights to connect directly to an [imaging lens](#). The adapter slides into a flange protruding from the back of the ring light. Select the ring light adapter with the threading that matches the front filter threading of the lens. All feature an anodized aluminum construction.

**Note:** Though Ring Light Filter Thread Adapters can work with a wide range of imaging lenses, the working distance and field coverage provided by the LED ring light must be considered. Vignetting may occur on very wide angle imaging lenses.

## Technical Information

Filter Thread	Imaging Lenses Available to Use with Adapters	Adapter Stock No.
M25.5 x 0.5	8.5/12/16/25/35/50/75mm <a href="#">C Series Fixed Focal Length Lenses</a>	<a href="#">#56-523</a>
M30.5 x 0.5	18mm and 25mm <a href="#">DG Series FFL</a> , <a href="#">28mm Rodagon</a> , <a href="#">MegaPixel Fixed Focal Length</a> (vignetting may occur with large format sensors), <a href="#">Compact VIS-NIR Lenses</a> (vignetting may occur with large format sensors)	<a href="#">#56-089</a>
M34.5 x 0.5	<a href="#">3.3X Macro Zoom Lens</a>	<a href="#">#56-090</a>
M37 x 0.75	<a href="#">MMS®</a> , 35mm <a href="#">DG Series FFL</a> , 0.50X and 1.0X <a href="#">SilverTL™ Telecentric</a>	<a href="#">#56-091</a>
M39 x 0.5	50mm <a href="#">DG Series FFL</a>	<a href="#">#56-092</a>
M40.5 x 0.5	<a href="#">7X Close Focus Zoom</a> (vignetting may occur with large format sensors or at lowest zoom settings), 35/50/60/80/105/135mm <a href="#">Rodagon Lenses</a> , 0.60X <a href="#">SilverTL™</a> <a href="#">Telecentric Lenses</a>	<a href="#">#56-093</a>
M43 x 0.75	<a href="#">55mm Telecentric</a> , 0.30X/0.40X/2.0X <a href="#">SilverTL™ Telecentric</a>	<a href="#">#56-094</a>
M46 x 0.75	<a href="#">10X Close Focus Zoom</a> (vignetting may occur with large format sensors or at lowest zoom settings), 0.25X <a href="#">SilverTL™ Telecentric</a>	<a href="#">#56-095</a>
M49 x 0.75	75mm <a href="#">DG Series FFL</a>	<a href="#">#56-096</a>
M52 x 0.75	<a href="#">6X Close Focus Zoom</a> (vignetting may occur with large format sensors or at lowest zoom settings), <a href="#">TECHSPEC® LS Series Fixed Focal Length Lenses</a>	<a href="#">#56-097</a>
M58 x 0.75	0.36X/0.5X <a href="#">GoldTL™ Telecentric</a> , 0.20X/4.0X <a href="#">SilverTL™ Telecentric</a>	<a href="#">#56-098</a>
M62 x 0.75	0.73X/1X <a href="#">GoldTL™ Telecentric</a> , 0.16X <a href="#">SilverTL™ Telecentric</a>	<a href="#">#56-099</a>
M72 x 0.75	0.18X/0.25X <a href="#">GoldTL™ Telecentric</a>	<a href="#">#56-100</a>

Compatible Ring Lights
<a href="#">Advanced Illumination Standard Working Distance LED Ring Lights</a>
<a href="#">Advanced Illumination Extended Working Distance LED Ring Lights</a>
<a href="#">Advanced Illumination Brightfield/Darkfield LED Ring Lights</a>
<a href="#">Advanced Illumination 5" Darkfield LED Illuminators</a>