

## Meadowlark Optics LC Variable Retarder, Uncompensated, 1" Dia 1200-1700nm



Stock **#72-839** **2 In Stock**

-

1

+

€1.230<sup>85</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €1.230,85 each                |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

### SPECIFICATIONS

#### General

**Type:**  
Liquid Crystal Variable Retarder, Uncompensated

**Note:**  
Item supplied with retardance vs voltage performance data. Coaxial cable with mating connector is provided. Controller ([#72-848](#) or [#72-](#)

849) required for operation.

Physical & Mechanical Properties

|             |                         |
|-------------|-------------------------|
| 9.4         | Clear Aperture CA (mm): |
| 25.40 ±0.13 | Diameter (mm):          |
| 31.24 ±0.13 | Thickness (mm):         |

Optical Properties

|                                          |                                         |
|------------------------------------------|-----------------------------------------|
| AR-Coat                                  | Coating:                                |
| Optical Quality synthetic fused silica   | Substrate: □                            |
| ≤ 0.5% per surface at 0°deg AOI          | Reflection (%):                         |
| 40-20                                    | Surface Quality:                        |
| ≤ 2                                      | Beam Deviation (arcmin):                |
| ≤ λ/4 @ 632.8nm                          | Transmitted Wavefront Distortion (RMS): |
| 1200 - 1700                              | Wavelength Range (nm):                  |
| 500 W/cm², CW 300 mJ/cm², 10 ns, visible | Damage Threshold, Reference:            |
| ~30nm to λ/2                             | Retardance Range:                       |

Threading & Mounting

|                    |        |
|--------------------|--------|
| Anodized Aluminium | Mount: |
|--------------------|--------|

Material Properties

|                        |                    |
|------------------------|--------------------|
| Nematic Liquid Crystal | Retarder Material: |
|------------------------|--------------------|

Environmental & Durability Factors

|         |                             |
|---------|-----------------------------|
| 0 to 50 | Operating Temperature (°C): |
|---------|-----------------------------|

Regulatory Compliance

|                      |                             |
|----------------------|-----------------------------|
| <a href="#">View</a> | Certificate of Conformance: |
|----------------------|-----------------------------|

PRODUCT DETAILS

- Enable Precision Electrical Control of Polarization
- Multiple Options for UV to NIR wavelengths
- Compatible with [Meadowlark Optics Liquid Crystal Controllers](#)

Meadowlark Optics Liquid Crystal Variable Retarders enable precise electrical control of polarization through variation of effective birefringence with applied voltage. This alters the input polarized light to any chosen elliptical, linear, or circular polarization. These retarders are constructed using a birefringent nematic liquid crystal material between optically flat fused silica windows coated with transparent conductive Indium Tin Oxide (ITO) for maximum transmission within a specified wavelength range. Meadowlark Optics Liquid Crystal Variable Retarders are ideal for active polarization control in metrology and medical applications such as stress analysis, pharmaceutical ingredient analysis, and biological microscopy. For uncompensated retarders, there will be a residual retardance of around 30nm at high voltage.

**Note:** These variable retarders should be electrically driven with an AC waveform with no DC component to prevent ionic buildup which can damage the liquid crystal layer. For control, a 2 kHz square wave of adjustable amplitude is required. The [Meadowlark Liquid Crystal Analog and Digital Controllers](#) ensure the drive requirements are met and are recommended for use.

Meadowlark Optics Liquid Crystal Variable Retarders enable the precision electrical control of polarization through the variation of effective birefringence with applied voltage, altering the input polarized light to any chosen elliptical, linear, or circular polarization. As voltage is increased, retardance is decreased. For uncompensated retarders, there will be a residual retardance of around 30nm at high voltage.

These retarders are constructed using a birefringent nematic liquid crystal material between optically flat fused silica windows coated with transparent conductive Indium Tin Oxide (ITO) for maximum transmission within a specified wavelength range.

Each Meadowlark Optics Liquid Crystal Variable Retarder is supplied with retardance vs voltage performance data for the specified wavelength range, and a coaxial cable with mating connector is provided for easy attachment to one to Meadowlark Optics Liquid Crystal Controllers.

These variable retarders should be electrically driven with an AC waveform with no DC component to prevent ionic buildup which can damage the liquid crystal layer. For control, a 2 kHz square wave of adjustable amplitude is required.