

[See all 6 Products in Family](#)

Norland Electronic Adhesive NEA 123L, 10cc Dispensing Barrel

See More by [Norland](#)



Stock **#70-101** **2 In Stock**

-

1

+

€39⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-11	€39,50 each
Qty 12-19	€35,60 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
0.34	Size (oz):
NEA 123L	Norland Number:
12 months	Shelf Life:
Barrel	Type:

Typical Applications: Ideal for tacking, filling, sealing or bonding precision components or wires in place	
Note: Contains 10g of adhesive	

Optical Properties

Absorption Range (nm):
320 - 380

Material Properties

Glass Bonding:	Excellent
Metal Bonding:	Good
Plastic Bonding:	Good/Excellent
Viscosity (cps):	8000

Environmental & Durability Factors

Operating Temperature (°C):
-150 to +150 (after cured)

Regulatory Compliance

RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 251:	Compliant

Product Details

- Single Component UV Curing Adhesives
- Excellent Adhesion to Glass, Metals, and Plastic
- Ideal for Potting, Sealing, and Fastening

Norland Electronic Adhesives are single component UV curing adhesives that form electrically insulating bonds when cured. These adhesives are designed for fast, precision bonding in electronic assembly applications and have excellent adhesion to glass, metals, and plastics. Each adhesive also contains a heat catalyst that can quickly cure areas that cannot be exposed to UV light. Norland Electronic Adhesives are ideal for use with circuit boards, opto-electronic devices, or other electronics for potting, sealing, wire tacking, or fastening.

Note: NEA 121 and 123 may cause skin irritation and prolonged contact with skin should be avoided; [fingercots or gloves](#) are recommended when applying these adhesives. The curing process is highly exothermic – bulk material should never be exposed to high heat or ultraviolet light.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools