

[See all 48 Products in Family](#)

# Norland Optical Adhesive NBA 108H, 100g Bottle

See More by [Norland](#)



Norland Optical Adhesive NBA 108H, 100g Bottle

Stock **#17-363** **4 In Stock**

⊖ 1 ⊕ €108<sup>00</sup>

ADD TO CART

Volume Pricing	
Qty 1-4	€108,00 each
Qty 5-11	€97,20 each
Qty 12+	€92,40 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

## General

3.52 **Size (oz):**

108H **Norland Number:**

4 months **Shelf Life:**

Bottle **Type:**

**Typical Applications:**  
Temporary bonding of lenses to metal polishing mounts

**Note:**  
Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.  
Liquid adhesives cannot be put in a vacuum because it will remove the stabilizers and sensitizers causing the adhesive to not cure properly.

UV and/or Heat **Cure:**

## Optical Properties

1.51 @ 589nm **Index of Refraction ( $n_d$ ):**

350 - 380 **Absorption Range (nm):**

## Material Properties

Excellent **Glass Bonding:**

Excellent **Metal Bonding:**

Fair **Plastic Bonding:**

550 **Viscosity (cps):**

Glass to Metal **Bonding Type:**

6 **Energy for Full Cure ( $J/cm^2$ ):**

## Environmental & Durability Factors

Hard & Resilient **Durability:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 251:**

## Product Details

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

## Technical Information

**NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES**

Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.