

[See all 1 Products in Family](#)

Optotune Electrically Focus Tunable lens 12mm CA, VIS coated, C mount | EL-12-30-TC-VIS-16D-C



Stock #78-515 [CONTACT US](#)

- 1 + €965⁰⁰

[ADD TO CART](#)

Volume Pricing

Qty 1+	€965,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Specialty Lens

Type:

>1,000,000,000

Lifecycles:

EL-12-30-TC-VIS-16D-C

Model Number:

Response Time (ms):

Physical & Mechanical Properties

Clear Aperture CA (mm):

11.6

Outer Diameter (mm):

47.0

Thickness (mm):

5.80

Optical Properties

Substrate:

Low Dispersion Polymer

Coating:

BBAR (420-950nm)

Wavelength Range (nm):

420 - 950

Abbe Number (v_d):

100.00

Focus Range (mm):

-6 to +10 diopter

Index of Refraction (n_d):

1.450

Transmitted Wavefront Error, RMS:

Vertical: $0.15\lambda@525\text{nm}$ Horizontal: $0.25\lambda@525\text{nm}$

Electrical

Current (mA):

-250 to 250, -300 to 300 abs. max

Power Consumption (W):

0.94

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Fast Rise and Settling Times of 3ms & 10ms
- Low Temperature Sensitivity $<0.01\text{dpt}^\circ\text{C}$
- Low Power Consumption of 55mW for a 5 Diopter Range

Optotune Focus Tunable Lenses 12mm Clear Aperture Hirose Connector combine our Optotune Electrically Focus Tunable Lenses with C-Mount compatible housings to ease mechanical integration into imaging systems. This lens features a versatile focal power range of -6 to +10 diopters with exceptional precision in a slim housing that adds only 5.8mm to the optical axis. Optimized for fast response times and low thermal sensitivity, the liquid lens can switch from a flat zero-state into a plano-concave or plano-convex lens in 3ms and remain stable with a $<0.01\text{dpt}^\circ\text{C}$ sensitivity. Optotune Focus Tunable Lenses 12mm Clear Aperture Hirose Connector are ideal for replacing multi-lens or zoom systems in machine vision, microscopy, and optical coherent tomography (OCT) applications. The protective cover glass is AR coated to maximize transmission from 420 – 950nm.